

Item Number 63082A**Boswell**

LED Mini Pendant Oil Rubbed Bronze Finish
with Highlights Prismatic Frosted Acrylic
Lens

Specifications

- Height: 41.34"
- Diameter: 8.75"
- Includes (1) Medium (E26) Base Lamp,
9 Watt Omni A19 LED
- Hours: 25000
- Life (years)*: 22.8
- Fixture Lumens: 800
- Kelvin: 3000
- Equivalent Incandescent Wattage: 60W
- Includes (3) 9.5" long rods
to customize hanging length




Installation

Refer to instruction manual for installation and additional warnings.
Consult a qualified electrician if unsure how to proceed.

Warranty Information - 5 Year Limited Warranty

This Westinghouse Lighting Fixture is warranted against defects in material and workmanship
for a period of Five Years from purchase date.


Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.

Item Number 63082A
Omni-Directional LED Dimmer Compatibility

| Brand | Model |
|----------------|---|
| Legrand | DRD4-B(Digital) |
| Leviton | R62-6683-IW, C20-6681-IW, R01-RPI06-1LI, 6674-10W, R02-6615-POW, 1PE04-1LZ, R50-6602-IW, 6633, IPL06, R15-IPI06-1SE |
| Lutron | TTCL-100H-WH, D-600PH-DK, DVLV-600P-WH, NTLV-600-WH, DVELV-300P-WH, DV-603PG-WH, NLV-600-WH, CTCL-153PDH, D-603PH, TT-300NLN-WH, MRF2-3PD-1-1WH(Digital), MA-600-WH(Digital), MAW-600(Digital), MRF2-6ND-120-WH(Digital), RRD-10ND-WH(Digital), VTELV-600M-B-WH(Digital), MAELV-600-WH(Digital), MRF2-6ELV-120-WH(Digital), AYCL-153P-WH, AYLV-600P-WH, TG-603PGH-WH, S-600PR-WH, CTCL-153P-WH, MACL-153M-WH (Digital), DVCL-153P-WH, SCL-153PH-WH-C, LGCL-153PLH-WH-C, TGCL-153PH-WH-C |
| Pass & Seymour | CD703-PW, CDLV703-P, D703-PTC, DLV703-P |

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 WESTINGHOUSE, AND INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.