SPECIFICATION SHEET

STYLE: 250-26-0015

P65

Bouton® Optical Zenon Z13R™

Rimless Safety Readers with Clear Temple, Clear Lens and Anti-Scratch Coating - +1.50 Diopter

- Lightweight, rimless design provides all day user comfort
- Flexible, rubber tip temples provide a secure fit without uncomfortable pressure points
- Molded nose bridge design to fit the vast majority of users
- Variety of lenses available to fit your application
- 10 Base curve lens
- +1.50 Diopter
- Meets ANSI Z87.1+
- **WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

Technical Data

Color	Clear
Sizes Available	OS
Packaging	Bagged Each
Packed	72 Pair/Case
Case Dimensions (in)	18.86 x 10.12 x 9.53
Case Weight (lbs)	6.83
Country of Origin	Taiwan
Lens	Clear
Frame Style	Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch
Bridge	Molded
Temple	Rubber Tips
Diopter	1.50
Base Curve	10
Certifications	ANSI Z87.1, TAA Compliant
Product Circularity	Recycled via Terracycle

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-03

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS COATING	UPC	UPC (INNER)	UPC (CASE)
250-26-0010	Clear	Clear	Clear	AS	616314156625	01616314156624	02616314156623
250-26-0012	Clear	Clear	Clear	AS	616314156632	01616314156631	02616314156630
250-26-0015	Clear	Clear	Clear	AS	616314156649	01616314156648	02616314156647
250-26-0017	Clear	Clear	Clear	AS	616314156656	01616314156655	02616314156654
250-26-0020	Clear	Clear	Clear	AS	616314156663	01616314156662	02616314156661
250-26-0022	Clear	Clear	Clear	AS	616314156670	01616314156679	02616314156678
250-26-0025	Clear	Clear	Clear	AS	616314156687	01616314156686	02616314156685
250-26-0030	Clear	Clear	Clear	AS	616314156694	01616314156693	02616314156692

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-03