



TEGERA® 295

Learn more

POPULAR QUALITY LEATHER WATERPROOF GLOVE

Professional and most-popular waterproof winter glove for cold & wet outdoor work. The ergonomic design provides a superior all-day comfort, reducing hand fatigue. The combination of durable leather and 40 g Thinsulate™ technology makes it the ideal glove for cold insulation in many different robust jobs.

CHARACTERISTICS

- Extremely good fingertip sensitivity
- Extra flexible
- Durable
- Perfect fit
- Good grip
- Extra comfortable
- Warm

FUNCTIONS

- Reinforced fingers and thumb
- Waterproof

AQUATHAN®

Thinsulate™ INSULATION

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Contact with dirt, Abrasion injuries, Scratches, lacerations, Grazes, Contact with cold, Contact with damp, Contact with moisture, Blisters

PRIMARY ENVIRONMENTS OF USE

Cold environments, Wet environments

PRIMARY AREAS OF USE

Machine operating, Building and construction, Carpentry, Transport work, Machine driving, Airport work, Repair work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Transportation and logistics, Electricity and gas supply, Building and construction, Mining and quarrying, Warehousing

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE All-round work gloves, Assembly gloves, Cold insulation gloves
CATEGORY Cat. II
PALM MATERIAL Full grain goatskin
BACK MATERIAL Spandex
LINING Winter-lined
LINING MATERIAL Thinsulate™ 40g
LENGTH 220-315 mm
DEXTERITY 4
COLOUR White
PAIRS PER: BUNDLE/CARTON 6/60
DISPLAY TYPE Hook with hangtag
FASTENING Elasticated 360°
INNER MATERIAL SPECIFICATION Polyester
MIDDLE MATERIAL SPECIFICATION Thermoplastic polyurethane (TPU)
OUTER MATERIAL SPECIFICATION Leather, Elastane, Polyester

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018 2121X

EN 511:2006 121

ANSI 3 ABR

FEATURES

Warm lining

Waterproof

Windproof

SIZE		ARTICLE NUMBER	EAN
6	XS	295-6	7340118313061
7	S	295-7	7340118313092
8	M	295-8	7392626034181
9	L	295-9	7392626034198
10	XL	295-10	7392626034204
11	XXL	295-11	7392626034211
12	3XL	295-12	7392626037281
13	4XL	295-13	7340118343785
14	5XL	295-14	7340118327099
15	6XL	295-15	7340118327211

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.