



ATG® MaxiCut® Ultra™

Seamless Knit A3 Engineered Yarn Glove with Premium Nitrile Coated MicroFoam Grip on Palm, Fingers & Knuckles - Micro Dot Palm - Touchscreen

- Innovative fibres - ATG® sources their base ingredients to develop their own unique high performance yarns and fibers that offer cut protection while maintaining high levels of comfort.
- Reinforcement - between the thumb and forefinger, improves cut resistance and extends glove life in an inherently weak area.
- 360° breathability - patented Nitrile MicroFoam coating offers 360° breathability, making it the most breathable glove on the market today.
- Form, fit and feel - mimics the "hand at rest", reducing hand fatigue and increasing comfort.
- Touchscreen compatible to allow the user to operate a touch screen phone or device without removing gloves
- Latest knitting technology - utilized to produce smooth and rounded fingertips, improving fingertip sensitivity.

Applications

- Good Grip, Durable Coating, Premium Performance
- Mechanical Equipment Maintenance and Repair
- Handling, Assembly and Sorting
- Finishing and Parts Inspection
- Industrial Applications
- Precision Construction Jobs



Technical Data

Color	Blue
Sizes Available	XS-2XL
Packaging	Bulk Pack
Case Weight (lbs)	0.00
Country of Origin	Sri Lanka
Liner Material	Engineered Yarn
Coating	Nitrile
Coating Color	Black
Coating Coverage	Palm, Fingers & Knuckles
Grip	Dot
Gauge	15
Cuff	Knit Wrist
Construction	Coated Seamless Knit, Touchscreen Compatible, Reinforced Thumb Crotch
Certifications	21 CFR, Latex Free
Product Circularity	Recycled via Terracycle Reusable / Launderable

Performance Data

Cut Level	A3
ANSI Abrasion Level	4
ANSI Puncture Level	3
EN 388	4542C

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-07-24

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
44-3455/XS	Blue	XS	616314178467	01616314178466	02616314178465
44-3455/S	Blue	S	616314178375	01616314178374	02616314178373
44-3455/M	Blue	M	616314178368	01616314178367	02616314178366
44-3455/L	Blue	L	616314178351	01616314178350	02616314178359
44-3455/XL	Blue	XL	616314178450	01616314178459	02616314178458
44-3455/XXL	Blue	2XL	616314178474	01616314178473	02616314178472