



PIP® Traverse™

Vented, Industrial Climbing Helmet, Type I, ABS Shell, EPS Foam Impact Liner, Wheel Ratchet Adjustment, with 4-Point Chin Strap

- Ultra-lightweight vented shell made with ABS material provides superior protection while promoting air circulation
- EPS foam impact liner helps absorb the forces of top-of-head, front, side, and rear impacts
- Includes an adjustable 4-point cross-over chin strap with quick release buckle for a safe and secure fit
- Rugged SURE-LOCK adjustable wheel ratchet ensures proper suspension performance and fit for all head sizes
- Inner suspension includes comfortable padding for above the brow line
- Meets ANSI Z89.1-2014 Type I, Class C

Technical Data

Color	White, Orange, Navy, Black, Hi-Vis Yellow, Yellow, Gray, Dark Green, Red
Sizes Available	OS
Packaging	Case
Packed	18/Case
Case Dimensions (in)	28.35 x 11.61 x 30.71
Case Weight (lbs)	29.17
Country of Origin	China
Shell Material	ABS
Shell	Vented
Brim Style	Cap Style
Brim Length	Micro
Size Adjustment	Wheel Ratchet
Suspension	Foam Cradle System
Chin Strap	4-Point Polyester
Sweatband	Polyester EVA
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, EN 12492

Performance Data

ANSI Type	Type I
Electrical Class	Class C

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP1490RV-11	Black	OS	616314851940	10616314851947	20616314851944
280-HP1490RV-04	Dark Green	OS	616314852466	10616314852463	20616314852460
280-HP1490RV-09	Gray	OS	616314907005	10616314907002	20616314907009
280-HP1490RV-44	Hi-Vis Yellow	OS	616314852428	10616314852425	20616314852422
280-HP1490RV-08	Navy	OS	616314852503	10616314852500	20616314852507
280-HP1490RV-03	Orange	OS	616314852183	10616314852180	20616314852187
280-HP1490RV-15	Red	OS	616314852381	10616314852388	20616314852385
280-HP1490RV-01	White	OS	616314851865	10616314851862	20616314851869
280-HP1490RV-02	Yellow	OS	616314852060	10616314852067	20616314852064