HAMMER HEAD 2®

BASETEK®

02-008HH
SPECIFICATION SHEET



ANSI/ISEA 105

A2

X X

EN388

4242B

SPECIFICATIONS:

- **Liner Materials:** 13g Salt & Pepper HDPE Basetek® A2 Liner
- **Coating Materials:** Gray Polyurethane
- **Wrist Design:** Continuous knit
- **Origin:** PRC
- **Sizes:** XS-2X

Armor Guys Reference Number: 02-008HH

PACKAGING:

GLOVE SIZE	XS	S	M	L	XL	XXL
CUFF COLOR	Purple	Red	Yellow	Brown	Black	Blue
PER CASE	12DZ	12DZ	12DZ	12DZ	12DZ	12DZ
CASE WEIGHT	16.28 lbs	16.50 lbs	17.38 lbs	18.37 lbs	23.50 lbs	26.07 lbs

PERFORMANCE LEVEL:

EN388: 4242B – EN Level 2 Cut Resistance

ABRASION	0	1	2	3	**4**	5
CUT	0	1	**2**	3	4	5
TEAR	0	1	2	3	**4**	5
PUNCTURE	0	1	**2**	3	4	5
CUT TDM TEST	A	**B**	C	D	E	F

⚠ This product can expose you to N,N-Dimethylformamide which is known to the State of California to cause cancer. For more information go to www.P65warnings.ca.gov

ATTRIBUTES:

- 13g Salt & Pepper HDPE Basetek® A2 Liner
- Gray Polyurethane Palm Coating

FEATURES:

- Positive grip in dry & light oil environments

APPLICATIONS:

- Automotive manufacturing
- Appliance manufacturing
- Construction
- Sheet metal handling
- Small parts assembly

CATEGORY:

- **Basetek®**

CARE INSTRUCTIONS:

Recommended washing temperature is between 40°C and 60°C (104 - 140°F) with mild detergent.

The drying process may cause felting on the fabric surface. Drying temperatures should not exceed 70°C (158°F).

TECHNOLOGIES:

BASETEK®

Innovative Fiber Technology

ARMOR GUYS