Project / Job Name:

Location:

Fixture Type:

Notes:

**67-571** - Running Man Green Combo Exit Sign/Emergency Light; 120/347V; 2HR backup; Single/Dual Face; Universal Mounting; Wet Location; Remote-Capable; White Finish

WET LOCATION · RoHS COMPLIANT · IP 65

## GENERAL

| | |
|---|---|
| Company | SATCO |
| EA Height | 14.57 |
| EA Width | 3.35 |
| EA Length | 13.78 |
| Bulb Included | Integrated |
| Material | Thermo Plastic |
| Fixture Type | Exit Sign |
| Product Notes | Ni-MH Battery; 120 minute discharge time; Remote Compatible; 24 Hour Recharge Time |
| Status | Active |
| Style | Utility |
| Total Harmonic Distortion | 35%-45% |
| CCT Selectable | No |
| Wattage Selectable | No |
| Finish Family | White |
| Additional Info | Remote Capable Power Rating: 3.6V/1.5W |
| Amps | 0.033/0.012A |
| Has Camera | No |
| IOT Enabled | No |
| Lens Finish | Clear |
| Lens Material | Polycarbonate (PC) |
| Power Factor | 0.8 |
| SDS Class | LED_Fixture |
| Sloped Ceiling Compatible | No |
| Indoor Outdoor | Indoor and Outdoor |
| Product Technology | LED |
| Serviceable Battery | No |
| Battery Indicator | No |
| Digital Display | No |

## ELECTRICAL

| | |
|---|---|
| CCT (Kelvin Temp) | 5700K |
| Dimmable | Non-Dimmable |
| CRI | 80+ |
| Operating Frequency | 60Hz |
| Operating Temp | +32F to +122F (0C to +50C) |
| Lumens | 160L |
| Volts | 120V/347V |
| Watts | 4W |
| Battery Chemistry | Ni-MH |

## PHYSICAL

| | |
|---|---|
| Lamp Base | Integrated |
| Finish | WHITE |
| ANSI Base | Integrated |
| Lamp Type | Integrated LED |
| Mounting Procedure | Universal |

## ADDITIONAL INFO

| | |
|---|---|
| Warranty | 2-Years |

## PACKAGING

| | |
|---|---|
| UPC | 045923675935 |
| Case Cube | 1.8116 |
| Case Height | 14.37 |
| Case Length | 15.16 |
| Case Quantity | 4 |
| Case UPC | 10045923675932 |
| Case Weight | 25.57 |
| Case Width | 14.37 |
| EA Cube | 0.3892 |
| EA Height | 14.57 |
| EA Length | 13.78 |
| EA Quantity | 1 |
| EA Weight | 5.51 |
| EA Width | 3.35 |
| Pack Type | Box |
| Web Height | 13.91 |
| Web Width | 13.0 |

## COMPLIANCE

| | |
|---|---|
| CA Prop 65 | Lead |
| IP Rating | IP65 |
| Location Rating | Wet |
| ROHS Compliant | Yes |
| Safety Listing | CSAus |
| California Ban | Non-Compliant |
| Title 20 | No |
| T24/JA8 Compliant | No |



© Satco Products, Inc.
All rights reserved 2026