



G-Tek® ECO Series™

Seamless Knit A4 Dyneema® Phoenix Blended Glove with Nitrile Coated Foam Grip on Palm & Fingers

- Seamless construction offers increased comfort and breathability
- Spun Dyneema® Phoenix & Spandex shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Bio-Based Dyneema fiber provides same performance & protection, while providing lower carbon footprint
- Dyneema® bio-based fibers equates to 450g of CO2 emissions reduction per pair when compared to traditional Dyneema® fibers
- Foam Nitrile coatings are breathable and durable, designed with a cell structure that disperse fluids on contact for an improved grip
- Knit Wrist helps prevent dirt and debris from entering the glove

Applications

- Secure Dry Grip and Oil Resistant
- Handling and Assembly of Medium to Large Parts and Materials
- Metal Fabrication
- Mechanical Equipment Maintenance and Repair
- Heavy to Medium Fastening and Anchoring



Technical Data

Color	Salt & Pepper
Sizes Available	S-2XL
Packaging	Pair Bagged Retail Ready
Packed	6 Dozen/Case
Case Dimensions (in)	11.81 x 12.60 x 15.75
Case Weight (lbs)	14.11
Country of Origin	China
Liner Material	Dyneema Phoenix
Coating	Nitrile
Coating Color	Black
Coating Coverage	Palm & Fingers
Grip	Foam
Gauge	13
Cuff	Knit Wrist
Construction	Coated Seamless Knit, Coreless Technology
Certifications	21 CFR
Product Circularity	Recycled via Terracycle Reusable / Launderable Contains Bio-Based Materials

Performance Data

Cut Level	A4
ANSI Abrasion Level	6
ANSI Puncture Level	3
EN 388	4X42DX

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-07-09

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
19-D334/S	Salt & Pepper	S	616314167799	01616314167798	02616314167797
19-D334/M	Salt & Pepper	M	616314167782	01616314167781	02616314167780
19-D334/L	Salt & Pepper	L	616314167775	01616314167774	02616314167773
19-D334/XL	Salt & Pepper	XL	616314167805	01616314167804	02616314167803
19-D334/XXL	Salt & Pepper	2XL	616314236686	01616314236685	02616314236684