



EAN:	4013288211934	Size:	66x23x4 mm
Part number:	05022670001	Weight:	4 g
Article number:	950 SPKS Multicolour	Country of origin:	CZ
		Customs tariff number:	82041100

- L-keys for hexagonal socket screws
- Hex-Plus allows socket head screws to live longer
- Colour coded, easy-to-grip plastic sleeve, even at low temperatures
- Hexagonal ballpoint on the long arm
- Wear-resistant size marking

High quality Wera L-keys with colour coded, convenient plastic sleeve. This means that the tool is quickly accessible and the ergonomic and pleasant handle is easy on the hands even at low temperatures. Hex-Plus L-keys provide larger contact surfaces on the screw head. The notching effect is thereby reduced to a minimum; the destruction of the screw head is almost eliminated. The ball on the long arm allows safe working even in difficult mounting positions. The BlackLaser surface treatment provides excellent surface protection, corrosion resistance and long life. Laser coated abrasion-resistant size markings on the L-keys for quick access.



Web link

<https://www.wera.de/en/05022670001>

Wera - 950 SPKS Multicolour
05022670001 - 4013288211934

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

L-keys with a thermoplastic sleeve



We questioned the classic L-key design, since all too often the screw head recess is rounded out, meaning screws can no longer be tightened or loosened - and so the user finds the L-key slipping out of the recess. Wera Hex-Plus tools have a larger contact surface in the screw head. The notching effects are reduced and thereby the deformation of the screws. At the same time, as much as 20 % more torque can be applied.



L-keys made from circular material fit into the hand better and allow less strenuous work over a longer period. Additionally, the rubber sleeve provides a pleasant grip, particularly in applications at low temperatures. Colour coding and large stamp enable the desired L-key to be easily located. Moreover, the round material keys are more robust, particularly where smaller sizes are concerned.

Hex-Plus



Hexagon screws can endure a problem because the contact surfaces delivering the power from the conventional tool, is transferred to the screw via very small surface areas. The consequence: the screw can become damaged (rounding out). Hex-Plus tools have a greater contact surface that prevents this from happening! At the same time, as much as 20 % more torque can be applied. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!

Ball tip



The spherical drive profile means that it is possible to swivel the axis of the tool to that of the screw, and therefore enable angled, "around-the-corner" screwdriving jobs.

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Web link

<https://www.wera.de/en/05022670001>

Wera - 950 SPKS Multicolour
05022670001 - 4013288211934

Wera Werkzeuge GmbH
Korzer Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Further versions in this product family:

		 mm	 mm	 mm	 inch	 inch
05022678001	iceblue_277C	1.5	50	14	2"	9/16"
05022670001	gruen_363C	2.0	56	16	2 7/32"	5/8"
05022671001	leuchtgruen_375C	2.5	63	19	2 1/2"	3/4"
05022672001	leuchtpink_232C	3.0	71	21	2 3/4"	27/32"
05022673001	gelb_123C	4.0	80	24	3 1/8"	1"
05022674001	leuchtorange_152C	5.0	90	27	3 1/2"	1 1/16"
05022675001	rot_200C	6.0	100	31	4"	1 1/4"
05022676001	pink_241C	8.0	112	37	4 7/16"	1 7/16"
05022677001	blau_307C	10.0	125	42	5"	1 11/16"

Web link

<https://www.wera.de/en/05022670001>

Wera - 950 SPKS Multicolour
05022670001 - 4013288211934

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de