

ArrowLink

Arrow Hart's factory terminated ArrowLink system revolutionizes device installation, unleashing ground breaking labor savings in installation and maintenance by eliminating leaded terminal connections and taping. Use ArrowLink on your next job to reduce labor costs, eliminate installation errors, save money and win!


Features & benefits

6" #12 AWG ground lead with ring terminal and captive ground screw

Durable polycarbonate housing

Terminal accommodation #12 - #14 AWG, solid only


Copper alloy contacts for superior wire retention and minimized heat rise



How to order



1. Select a device to ArrowLink enable. Catalog pages identify available products—simply add an "M" to the catalog number and the devices will be factory enabled with the ArrowLink device-side connection



2. Choose from leaded or ArrowLink SPD connector versions



3. Place your order and get your ArrowLink devices in bulk packed boxes, shipped within 5 days of receipt of order!

Compliances, specifications and availability are subject to change without notice.

ArrowLink SPD benefits



50% Time savings:

SPD accelerates both rough-in & trim out installation



Efficient design:

Low profile connection with feed-through capability




30% Reduction

In wire volume inside the box versus wire lead terminal

ArrowLink modular connectors

ArrowLink SPD comparative labor savings analysis


Traditional pigtail installation



4:55/Receptacle

Total time required to install 500 pigtail devices:
40.97 Hours

ArrowLink SPD installation



2:25/Receptacle

Total time required to install 500 ArrowLink SPD devices:
20.13 Hours

Time saved with SPD
20.84 Hours

Leaded ArrowLink connectors


Device type	Description	Catalog no.
Switch	Solid wire leads – 120V	<input type="checkbox"/> MCS120SOL
	Stranded wire leads – 120V	<input type="checkbox"/> MCS120STR
	Solid wire leads – 277V	<input type="checkbox"/> MCS277SOL
	Stranded wire leads – 277V	<input type="checkbox"/> MCS277STR



MCS120SOL
Leaded ArrowLink connector

ArrowLink SPD connectors

Device type	Description	Catalog no.
Switch	Push-In	<input type="checkbox"/> MCS300PI



MCS300PI
ArrowLink SPD push-in terminal connector

ArrowLink accessories

Device type	Description	Catalog no.
Terminating cap	Circuit completer for job site testing	<input type="checkbox"/> MCS300TC
Circuit tester	Tests receptacle & ArrowLink connectors	<input type="checkbox"/> ALTESTER



ALTESTER
circuit tester

Compliances, specifications and availability are subject to change without notice.

www.eaton.com
www.eaton.com/arrowhart