



G-Tek® PolyKor® X7™

Seamless Knit PolyKor® X7™ Blended Glove with Impact Protection and NeoFoam® Coated Palm & Fingers

- Seamless construction offers increased comfort and breathability
- PolyKor® blended shell with X7™ technology offers very high cut resistance and durability
- NeoFoam® offers an incredibly secure grip in dry conditions, a versatile and flexible coating that provides breathability and a high degree of dexterity, ideal for handling and the assembly of parts
- Reinforced thumb crotch for extended glove life, enhanced comfort, increased abrasion resistance and added durability in a high-wear area
- Thermo Plastic Rubber (TPR) back-of-hand impact resistance to knuckles and fingers by dispersing impact force energy away from the bone, without sacrificing dexterity
- Touchscreen compatible to allow the user to operate a touch screen phone or device without removing gloves

Applications

- Secure Dry and Flexible Grip
- Handling, Assembly and Sorting of Small to Medium Parts and Materials
- Shipping, Receiving and Packaging
- Maintenance and Repair Operations




Technical Data

Color	Black
Sizes Available	M-2XL
Packaging	Pair Bagged Retail Ready
Packed	36 Pair/Case
Case Dimensions (in)	17.32 x 12.20 x 8.66
Case Weight (lbs)	14.77
Country of Origin	China
Liner Material	PolyKor X7
Coating	Neofoam
Coating Color	Black
Coating Coverage	Palm & Fingers
Grip	Neofoam
Gauge	18
Cuff	Knit Wrist
Impact Protection	Finger, Thumb, Back of Hand
Construction	Coated Seamless Knit, Touchscreen Compatible
Product Circularity	Reusable / Launderable

Performance Data

Cut Level	A7
ANSI Abrasion Level	4
ANSI Puncture Level	3
ANSI Impact Level	1
EN 388	4X42FP

Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-16

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
16-MP785/M	Black	M	616314267093	01616314267092	02616314267091
16-MP785/L	Black	L	616314267109	01616314267108	02616314267107
16-MP785/XL	Black	XL	616314267116	01616314267115	02616314267114
16-MP785/XXL	Black	2XL	616314267123	01616314267122	02616314267121