



<b>EAN:</b>	4013288019301	<b>Size:</b>	54x18x4 mm
<b>Part number:</b>	05024008001	<b>Weight:</b>	5 g
<b>Article number:</b>	967 TORX®	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82041100

- L-keys for recessed TORX® screws
- BlackLaser for high corrosion protection and long service life
- Laser-engraved and thereby wear-resistant size markings

High quality L-keys for recessed TORX® screws. The BlackLaser surface treatment provides outstanding surface protection, even against corrosion, and a long service life. The tools are quickly to hand thanks to the laser-engraved and thereby wear-resistant size markings on the L-keys.

**Web link**

<https://www.wera.de/en/05024008001>

Wera - 967 TORX®  
05024008001 - 4013288019301

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Size identification

Surface protection



The size of each L-keys has been engraved by a laser. In addition Take it easy L-keys have a colour coding according to sizes - for simple and rapid accessing of the required tool. Making it easy to find the right tool.

L-keys with BlackLaser surface treatment for outstanding surface protection and long service life. High corrosion protection.

Further versions in this product family:



mm



mm



inch



inch

		mm	mm	inch	inch
05024001001	TX 6	42	16	1 5/8"	5/8"
05024002001	TX 7	48	16	1 7/8"	5/8"
05024003001	TX 8	48	16	1 7/8"	5/8"
05024004001	TX 9	48	16	1 7/8"	5/8"
05024005001	TX 10	51	17	2"	21/32"
<b>05024008001</b>	<b>TX 15</b>	<b>54</b>	<b>18</b>	<b>2 1/8"</b>	<b>23/32"</b>
05024010001	TX 20	57	19	2 1/4"	3/4"
05024012001	TX 25	60	20	2 3/8"	25/32"
05024013001	TX 27	64	21	2 1/2"	27/32"
05024015001	TX 30	70	24	2 3/4"	1"
05024020001	TX 40	76	26	3"	1 1/32"

Web link

<https://www.wera.de/en/05024008001>

Wera - 967 TORX®

05024008001 - 4013288019301

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)