

Scotch® Barricade Tapes

Scotch® Buried Barricade Tape 300 Series

Scotch® Barricade Tapes 300 Series are effective and economical. One roll has sufficient length to mark a large area. Constructed of durable polyethylene plastic that prevents accidental tearing, the tapes have bold 2" black characters on bright background and are sure to attract attention and provide a clearly visible warning message. Different sizes and messages available.

Adhesive Material	None
Backing Material	Polyethylene Film
RoHS 2011/65/EU	Yes



Order No.	UPC	Text	Color	Length	Width	Thickness	Rolls per Case
302	051128-53461	CAUTION BURIED ELECTRIC LINE BELOW	Red	1000' (304,8 m)	3" (76,2 mm)	4 mil	8
303	051128-53462	CAUTION BURIED ELECTRIC LINE BELOW	Red	300' (91,44 m)	3" (76,2 mm)	4 mil	16
363	051128-57768	CAUTION HIGH VOLTAGE CABLE BURIED BELOW	Red	1000' (304,8 m)	3" (76,2 mm)	4 mil	8
364	051128-57769	CAUTION BURIED ELECTRIC LINE BELOW	Yellow	1000' (304,8 m)	3" (76,2 mm)	4 mil	8
365	051128-57770	CAUTION BURIED FIBER OPTIC LINE BELOW	Orange	1000' (304,8 m)	3" (76,2 mm)	4 mil	8
366	051128-57771	CAUTION BURIED CABLE TV LINE BELOW	Orange	1000' (304,8 m)	3" (76,2 mm)	4 mil	8
367	051128-57772	CAUTION BURIED TELEPHONE LINE BELOW	Orange	1000' (304,8 m)	3" (76,2 mm)	4 mil	8
368	051128-57773	CAUTION BURIED ELECTRIC LINE BELOW	Red	1000' (304,8 m)	6" (15,24 cm)	4 mil	4
369	051128-57774	CAUTION HIGH VOLTAGE CABLE BURIED BELOW	Red	1000' (304,8 m)	6" (15,24 cm)	4 mil	4
370	051128-57775	CAUTION BURIED ELECTRIC LINE BELOW	Yellow	1000' (304,8 m)	6" (15,24 cm)	4 mil	4
371	051128-57776	CAUTION BURIED FIBER OPTIC LINE BELOW	Orange	1000' (304,8 m)	6" (15,24 cm)	4 mil	4

Scotch® Detectable Buried Barricade Tapes 400 Series

Scotch® Detectable Buried Barricade Tapes 400 Series are designed for accurately locating and helping prevent damage to valuable underground utility installations. The tapes have an aluminum backing, which helps make underground assets easier to find when using a non-ferrous locator. Properly installed, these tapes may help avoid catastrophically inaccurate digging when locating utilities such as electrical lines and communication cables.

Adhesive Material	None
Backing Material	Aluminum Foil
RoHS 2011/65/EU	Yes



Order No.	UPC	Text	Color	Length	Width	Thickness	Rolls per Case
406	051128-57779	CAUTION BURIED ELECTRIC LINE BELOW	Red	1000' (304,8 m)	3" (76,2 mm)	5 mil	8
407	051128-57780	CAUTION BURIED FIBER OPTIC LINE BELOW	Orange	1000' (304,8 m)	3" (76,2 mm)	5 mil	8
408	051128-57781	CAUTION BURIED ELECTRIC LINE BELOW	Red	1000' (304,8 m)	6" (15,24 cm)	5 mil	4
409	051128-57782	CAUTION BURIED FIBER OPTIC LINE BELOW	Orange	1000' (304,8 m)	6" (15,24 cm)	5 mil	4
410	051128-57880	CAUTION BURIED TELEPHONE LINE BELOW	Orange	1000' (304,8 m)	3" (76,2 mm)	5 mil	8
411	051128-57881	CAUTION BURIED TELEPHONE LINE BELOW	Orange	1000' (304,8 m)	6" (15,24 cm)	5 mil	4
412	051128-57962	CAUTION BURIED HIGH VOLTAGE CABLE BELOW	Red	1000' (304,8 m)	3" (76,2 mm)	5 mil	8
413	051128-57964	CAUTION BURIED HIGH VOLTAGE CABLE BELOW	Red	1000' (304,8 m)	6" (15,24 cm)	5 mil	4