Standard Features

- Large 1-inch LCD display
- Dual-range capacity for increased precision from 0 to 22 lb
- Automatic precision change based on patient weight
- Accuracy within 5 g
- Unit of measure locking
- Recall function to view last weight
- Automatic shut-off for long battery life
- Built-in measuring tape 0 to 22.5 in (0 to 57 cm)
- Optional carrying case

Specifications

Capacity:
0 to 22 lb × 0.2 oz (0 to 10 kg × 5 g)
22 to 44 lb × 0.5 oz (10 to 20 kg × 10 g)

Power:
Four AA alkaline batteries (included)
or AC adapter (included)

Battery Type:
Four AA alkaline (included)

Approvals:
AC adapter: cULus

Warranty:
Two-year limited