



**MCR
SAFETY**

5309 Nitri-Chem Unsupported Specification Sheet

PRODUCT DESCRIPTION:

Nitrile gloves are three times more puncture resistant than rubber and can be used to offer superior resistance to many types of chemicals. This glove is an excellent alternative for individuals who experience allergic reactions to latex. The 5309 series is an unlined green nitrile glove that is 11 mil in thickness and 13 inches long. It provides excellent abrasion resistance and is made with component materials that comply with all federal regulations for food contact. The 5309 also has texture in the palm for additional grip. Looking for the best nitrile gloves? Look no further than MCR Safety!



FEATURES:

- 11 mil unlined green nitrile gloves
- 13 inch length
- Component materials comply with all federal regulations for food contact
- Industrial grade
- Textured grip
- Straight cuff
- Straight thumb
- Chemical resistant nitrile gloves

APPLICATIONS:

Bottling, Canning, Dairy, Painting, Poultry processing, Beef processing, Food

TECHNICAL DATA FOR: 5309

Series	Nitri-Chem	Overall Length	13 in.
Material Group	Unsupported	EN 388 : CE Score - Tear	3
Product Type	Unsupported	EN 388 : CE Score - Puncture	X
Glove Size	Large	ANSI Puncture	2
Material	Nitrile	ANSI Abrasion	6
Grade	Industrial Grade		
Lining	Unlined		
Thumb Style	Straight		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved



MCR
SAFETY


5309

Nitri-Chem

Unsupported Specification Sheet

Made In

Malaysia



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
5309	Large	13.00	4.39	N/A	16.356 lb.	1.363
5310	X - Large	13.35	4.7	N/A	16.704 lb.	1.392
5307	Small	12.56	3.74	N/A	13.740 lb.	1.145
5308	Medium	12.65	4.04	N/A	15.660 lb.	1.305
5311	XX - Large	13.44	4.7	N/A	18.996 lb.	1.583

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved