



## G-Tek® PolyKor® Seamless Knit PolyKor® Blended Glove with Hi-Vis Impact Protection and Nitrile Foam Grip on Palm & Fingers

- Seamless construction offers increased comfort and breathability
- PolyKor® blended shell is lightweight and provides excellent dexterity, tactile sensitivity, and cut resistance
- Foam Nitrile coatings are breathable and durable, designed with a cell structure that disperse fluids on contact for an improved grip
- Thermo Plastic Rubber (TPR) back-of-hand impact resistance to knuckles and fingers by dispersing impact force energy away from the bone, without sacrificing dexterity
- Bright coloring allows for more worker compliance and hand visibility
- Touchscreen compatible to allow the user to operate a touch screen phone or device without removing gloves




## Technical Data

|                      |                                                   |
|----------------------|---------------------------------------------------|
| Color                | Salt & Pepper                                     |
| Sizes Available      | M-2XL                                             |
| Packaging            | Pair Bagged Retail Ready                          |
| Packed               | 36 Pair/Case                                      |
| Case Dimensions (in) | 20.47 x 11.81 x 9.06                              |
| Case Weight (lbs)    | 14.77                                             |
| Country of Origin    | China                                             |
| Liner Material       | PolyKor                                           |
| Coating              | Nitrile                                           |
| Coating Color        | Black                                             |
| Coating Coverage     | Palm & Fingers                                    |
| Grip                 | Foam                                              |
| Gauge                | 13                                                |
| Cuff                 | Knit Wrist                                        |
| Impact Protection    | Finger, Thumb, Back of Hand                       |
| Construction         | Coated Seamless Knit, Touchscreen Compatible      |
| Product Circularity  | Recycled via Terracycle<br>Reusable / Launderable |

## Performance Data

|                     |        |
|---------------------|--------|
| Cut Level           | A2     |
| ANSI Abrasion Level | 5      |
| ANSI Puncture Level | 2      |
| ANSI Impact Level   | 1      |
| EN 388              | 4X41BP |

## Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

**PIP GLOBAL SAFETY | PROTECTION EMPOWERED™**

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | [www.pipglobalsafety.com](http://www.pipglobalsafety.com)

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-11

## SKU Information

| SKU            | COLOR         | SIZE | UPC          | UPC (INNER)    | UPC (CASE)     |
|----------------|---------------|------|--------------|----------------|----------------|
| 16-MP230HV/M   | Salt & Pepper | M    | 616314451232 | 10616314451239 | 20616314451236 |
| 16-MP230HV/L   | Salt & Pepper | L    | 616314451270 | 10616314451277 | 20616314451274 |
| 16-MP230HV/XL  | Salt & Pepper | XL   | 616314451317 | 10616314451314 | 20616314451311 |
| 16-MP230HV/XXL | Salt & Pepper | 2XL  | 616314451355 | 10616314451352 | 20616314451359 |