



EAN:	4013288122964	Size:	152x7x6 mm
Part number:	05059634001	Weight:	24 g
Article number:	840/4 Z Hex-Plus	Country of origin:	CZ
		Customs tariff number:	82079030

- For hexagonal socket head screws
- Hex-Plus allows socket head screws to live longer
- Tough for hard materials
- 1/4" hexagon drive (Wera connecting series 4)

Tough Wera bits for hexagonal socket screws, for universal use. Hex-Plus offers larger contact surfaces in the screw head. The notch effect is reduced to a minimum and the destruction of the screw is nearly eliminated. 1/4" hexagonal, suitable for holders as per DIN ISO 1173-F 6.3.

Web link
<https://www.wera.de/en/05059634001>

Wera - 840/4 Z Hex-Plus
05059634001 - 4013288122964

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Hex-Plus

Tough bits



Hexagon socket screws are a problem, because the contact surfaces that transfer the force of the tool to the screw are very narrow. The consequence: the head of the screw can be damaged, usually rounding out the recess. Hex-Plus tools have larger contact surfaces to prevent this, driving from the flats of the recess, rather than the corners. Good to know: Hex-Plus tools fit into every standard hexagon socket screw!



Tough Wera bits prevent the tip from breaking prematurely. Z-bits usually are the bit for universal screwdriving applications.

Further versions in this product family:

					
	mm	inch	mm	inch	mm
05160885001	0.9	-	50	2"	2.6
05059602001	1.5	-	50	2"	2.0
05059603001	2.0	-	50	2"	4.0
05059628001	2.0	-	89	3 1/2"	4.0
05059604001	2.5	-	50	2"	4.0
05059629001	2.5	-	89	3 1/2"	4.0
05059605001	3.0	-	50	2"	4.0
05059630001	3.0	-	89	3 1/2"	4.0
05380033001	3.0	-	152	6"	4.0
05059610001	4.0	-	50	2"	5.0
05059631001	4.0	-	89	3 1/2"	5.0
05059634001	4.0	-	152	6"	5.0
05059615001	5.0	-	50	2"	6.0
05059632001	5.0	-	89	3 1/2"	6.0
05059635001	5.0	-	152	6"	6.0
05059620001 ¹⁾	6.0	-	50	2"	5.0

Web link

<https://www.wera.de/en/05059634001>

Wera - 840/4 Z Hex-Plus
 05059634001 - 4013288122964

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

05059633001 ¹⁾	6.0	-	89	3 1/2"	-
05059636001 ¹⁾	6.0	-	152	6"	-
05059625001 ¹⁾	8.0	-	50	2"	-
05059637001 ¹⁾	8.0	-	89	3 1/2"	-
05350430001	-	0.05"	50	2"	2.5
05135090001	-	1/16"	50	2"	2.5
05135091001	-	5/64"	50	2"	3.0
05059660001	-	5/64"	89	3 1/2"	3.0
05135092001	-	3/32"	50	2"	3.0
05059661001	-	3/32"	89	3 1/2"	3.5
05135093001	-	7/64"	50	2"	3.5
05059662001	-	7/64"	89	3 1/2"	4.0
05135094001	-	1/8"	50	2"	4.0
05059663001	-	1/8"	89	3 1/2"	4.0
05380045001	-	1/8"	152	6"	4.0
05135095001	-	9/64"	50	2"	4.5
05059664001	-	9/64"	89	3 1/2"	4.5
05380046001	-	9/64"	152	6"	4.5
05135096001	-	5/32"	50	2"	5.0
05059665001	-	5/32"	89	3 1/2"	5.0
05380047001	-	5/32"	152	6"	5.0
05135097001	-	3/16"	50	2"	6.0
05059666001	-	3/16"	89	3 1/2"	6.0
05380048001	-	3/16"	152	6"	6.0
05135098001	-	7/32"	50	2"	-
05059667001	-	7/32"	89	3 1/2"	-
05380049001	-	7/32"	152	6"	-
05135099001	-	1/4"	50	2"	-
05059668001	-	1/4"	89	3 1/2"	-
05380050001	-	1/4"	152	6"	-
05346288001	-	5/16"	50	2"	-

1) Hexagonal blade

Web link<https://www.wera.de/en/05059634001>

Wera - 840/4 Z Hex-Plus
05059634001 - 4013288122964

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de