


Contents

	Page
1 2D Views	2
2 Configuration settings	3
3 Attachments / Technical document	5
4 Contact information	6

1 2D Views



2 Configuration settings

Configuration	
Buy Now	Buy Now
Part Number	RSR-2108
Description	Cord Grip Connector, aluminum, 3/4" NPT, cable range .438 - .500, Form Size 2
Minimum Cable Size (in)	0.438
Maximum Cable Size (in)	0.5
Cable Stranding	26 X # 30
Minimum Temperate - C°	-40
Minimum Temperate - F°	-40
Maximum Temperate - C°	121
Maximum Temperate - F°	249.8
Bushing Material	Neoprene
Washer Material	Zinc-Plated Steel
Body Material	Aluminum
REACH Compliant	Yes
ROHS Compliant	Yes
CSA Compliant	Yes
UL Compliant	Yes
Number of cables accomodated	1
Form Size	2
Conduit Size	3/4
Cord Grip Type	Straight
Country of Origin	United States
Unit Net Weight (lbs)	0.09
UPC	785411161082
UNSPSC	39121311

Bill of Materials Data	
Manufacturer	Remke Industries
Description	Cord Grip Connector, aluminum, 3/4" NPT, cable range .438 - .500, Form Size 2
Part Number	RSR-2108
Minimum Cable Size (in)	0.438
Maximum Cable Size (in)	0.5
Cable Stranding	26 X # 30
Minimum Temperate - C°	-40
Minimum Temperate - F°	-40
Maximum Temperate - C°	121
Maximum Temperate - F°	249.8
Bushing Material	Neoprene
Washer Material	Zinc-Plated Steel
Body Material	Aluminum

Bill of Materials Data	
REACH Compliant	Yes
ROHS Compliant	Yes
CSA Compliant	Yes
UL Compliant	Yes
Number of cables accomodated	1
Form Size	2
Conduit Size	3/4
Cord Grip Type	Straight
Country of Origin	United States
Unit Net Weight (lbs)	0.09
UPC	785411161082
UNSPSC	39121311
URL	https://www.remke.com/products/rsr-2108-rsr-series-straight-aluminum-cord-grip-34-npt-cable-range-438-500-form-size-2/

3 Attachments / Technical document

Please double click with left mouse button on a paper clip symbol to open a file. You could also save a file when you click the symbol with the right mouse button.

- Product Page 

4 Contact information

✉ Remke Industries
730 Lakeview Parkway
60061
IL
Vernon Hills
United States of America
✉ sales@remke.com
@ <https://www.remke.com>