



## ATG® MaxiFlex® Ultimate™

Seamless Knit Nylon/Elastane Glove with Nitrile Coated MicroFoam Grip on Palm, Fingers & Knuckles - Touchscreen

- MicroFoam Nitrile coatings are compatible with light oils and will provide a good grip and excellent abrasion resistance
- Touchscreen compatible to allow the user to operate a touch screen phone or device without removing gloves
- Knit Wrist helps prevent dirt and debris from entering the glove
- Silicone and Latex free
- 360° Breathability - Patented micro-foam nitrile coating offers 360° breathability, making it the most breathable glove on the market today
- 25% Thinner - Than most foam nitrile gloves on the market while offering twice the mechanical performance

## Applications

- Maximum Breathability, Comfort and Durability
- Handling, Assembly and Sorting of Small Parts and Materials
- Finishing and Parts Inspection



## Technical Data

|                     |                                              |
|---------------------|----------------------------------------------|
| Color               | Gray                                         |
| Sizes Available     | XXS-XL                                       |
| Packaging           | Bulk Pack                                    |
| Case Weight (lbs)   | 0.00                                         |
| Country of Origin   | Sri Lanka                                    |
| Liner Material      | Nylon, Elastane                              |
| Coating             | Nitrile                                      |
| Coating Color       | Black                                        |
| Coating Coverage    | Palm, Fingers & Knuckles                     |
| Grip                | MicroFoam                                    |
| Gauge               | 15                                           |
| Cuff                | Knit Wrist                                   |
| Construction        | Coated Seamless Knit, Touchscreen Compatible |
| Certifications      | 21 CFR, CFIA, Silicone Free, Latex Free      |
| Product Circularity | Reusable / Launderable                       |

## Performance Data

|                     |       |
|---------------------|-------|
| ANSI Abrasion Level | 4     |
| ANSI Puncture Level | 2     |
| EN 388              | 4131X |

## Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

**PIP GLOBAL SAFETY | PROTECTION EMPOWERED™**

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | [www.pipglobalsafety.com](http://www.pipglobalsafety.com)

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-16

### SKU Information

| SKU        | COLOR | SIZE | UPC          | UPC (INNER)    | UPC (CASE)     |
|------------|-------|------|--------------|----------------|----------------|
| 34-875/XXS | Gray  | XXS  | 616314020339 | 01616314020339 | 02616314020339 |
| 34-875/XS  | Gray  | XS   | 616314017995 | 01616314017995 | 02616314017995 |
| 34-875/S   | Gray  | S    | 616314018008 | 01616314018008 | 02616314018008 |
| 34-875/M   | Gray  | M    | 616314018015 | 01616314018015 | 02616314018015 |
| 34-875/L   | Gray  | L    | 616314018022 | 01616314018022 | 02616314018022 |
| 34-875/XL  | Gray  | XL   | 616314018039 | 01616314018039 | 02616314018039 |