



Technical Data



Bouton® Optical Adversary™ Semi-Rimless Safety Glasses with Black Frame, I/O Lens and Anti-Scratch Coating

- Lightweight, semi-rimless design provides all day user comfort
- Wraparound lens design with distortion-free viewing
- Bayonet temples with rubber tips provide a comfortable fit
- Temple tips curve out at ends for ease of placement on face
- Ribbed rubber nose pads offer a more secure fit
- Supplied with an adjustable neck cord
- 8 Base curve lens
- Meets ANSI Z87.1+
- **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	27.17 x 9.45 x 12.60
Case Weight (lbs)	13.23
Country of Origin	Malaysia
Lens	Indoor Outdoor
Frame Style	Semi-Rimless
Lens Color	Clear
Frame Fit	Round Face
Lens Coating	Anti-Scratch
Bridge	Rubber
Temple	Rubber Tips
Base Curve	8
Certifications	ANSI Z87.1
Product Circularity	Recycled via Terracycle

Applications

- Artificial Light
- Indoor/Outdoor Work
- Fork Lift Operation

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-06

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-28-0000	Black	Clear	Clear	AS	616314065835	01616314065834	02616314065833
250-28-0001	Black	Tinted	Gray	AS	616314065828	01616314065827	02616314065826
250-28-0002	Black	I/O	Clear	AS	616314068942	01616314068941	02616314068940
250-28-0003	Black	Tinted	Light Blue	AS	616314065842	01616314065841	02616314065840
250-28-0006	Black	Mirror	Silver	AS	616314068928	01616314068927	02616314068926
250-28-0009	Black	Tinted	Amber	AS	616314068935	01616314068934	02616314068933
250-28-0020	Black	Clear	Clear	AS/AF	616314065811	01616314065810	02616314065819
250-28-0021	Black	Tinted	Gray	AS/AF	616314068959	01616314068958	02616314068957

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated