



PIP® Kilimanjaro™

ANSI Type II Full Brim Safety Helmet with HDPE Shell Vented and Mips® Brain Protection System, 4-Point Textile Suspension, Wheel Ratchet Adjustment and 4-Point Chinstrap

- Lightweight HDPE shell made with UV stabilized High Density Polyethylene (HDPE) reduces worker fatigue
- EPS foam liner provides front, rear and lateral protection from impact and penetration
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- Mips® (Multi-directional Impact Protection System) Brain Protection System for Industrial Safety Helmets is a low frictional layer designed to reduce rotational motion transferred to the head from angled impacts
- Factory installed 4-point Fidlock chin strap 280-HP542MC Included
- SURE LOCK wheel adjustment system for one hand size adjustments

Technical Data

Color	Red, White, Black, Hi-Vis Orange, Sky Blue, Hi-Vis Yellow, Navy, Gray, Orange, Yellow, Dark Green, Royal
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Weight (lbs)	0.00
Country of Origin	Canada
Shell Material	HDPE
Shell	Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	4 Point Nylon Webbing Cradle
Chin Strap	4-Point Polyester
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Construction	MIPS Technology
Certifications	TAA Compliant

Performance Data

ANSI Type	Type II
Electrical Class	Class C

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP642RVM-CH-11	Black	OS	198987041069	10198987041066	20198987041063
280-HP642RVM-CH-04	Dark Green	OS	198987041076	10198987041073	20198987041070
280-HP642RVM-CH-09	Gray	OS	198987041083	10198987041080	20198987041087
280-HP642RVM-CH-31	Hi-Vis Orange	OS	198987041090	10198987041097	20198987041094
280-HP642RVM-CH-44	Hi-Vis Yellow	OS	198987041106	10198987041103	20198987041100
280-HP642RVM-CH-08	Navy	OS	198987041113	10198987041110	20198987041117
280-HP642RVM-CH-03	Orange	OS	198987041120	10198987041127	20198987041124
280-HP642RVM-CH-15	Red	OS	198987041137	10198987041134	20198987041131
280-HP642RVM-CH-17	Royal	OS	198987041144	10198987041141	20198987041148
280-HP642RVM-CH-07	Sky Blue	OS	198987041151	10198987041158	20198987041155
280-HP642RVM-CH-01	White	OS	198987037574	10198987037571	20198987037578
280-HP642RVM-CH-02	Yellow	OS	198987041168	10198987041165	20198987041162