



TEGERA® 577

Learn more

CUT RESISTANT GLOVE, WARM AND WATERPROOF

Cut resistant glove, level C, fully lined and warm, waterproof. Perfect fit with a good grip and good fingertip sensitivity. Reinforced fingertips and reinforced index finger. Suitable with touchscreen.

CHARACTERISTICS

- Good fingertip sensitivity
- Extra flexible
- Good grip
- Perfect fit
- Warm

FUNCTIONS

- For touchscreen
- Chrome free
- Reinforced index finger
- Reinforced fingertips
- Waterproof

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Prevents risk of: , Chrome allergy, Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with moisture, Contact with cold

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Cold environments, Wet environments, Harsh environments

PRIMARY AREAS OF USE

Building and construction, Warehouse work, Sanitation

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Oil and gas extraction, Automotive manufacturing, Building and construction, Mining and quarrying, Pulp and paper

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE All-round work gloves, Assembly gloves, Cold insulation gloves, Cut resistant gloves
CATEGORY Cat. II
PALM MATERIAL Synthetic leather
BACK MATERIAL Polyester
LINING Fully lined
LINING MATERIAL HPPE, Polyester, Stainless steel fibre yarn
LENGTH 225-260 mm
DEXTERITY 5
GRIP DESIGN Structured
COLOUR Grey
PAIRS PER: BUNDLE/CARTON 6/72
DISPLAY TYPE Hook with hangtag
FASTENING Hook-and-loop
CUT RESISTANCE (EN ISO 13997) Cut resistance level C
CUT RESISTANCE (EN ISO 13997) TDM: 15.7 N
INNER MATERIAL SPECIFICATION Polyester
MIDDLE MATERIAL SPECIFICATION Polyurethane, HPPE (High performance polyethylene)
OUTER MATERIAL SPECIFICATION Polyurethane, Polyester

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 2X22C

EN 511:2006 111

ANSI A4 CUT

ANSI 3 ABR

FEATURES

For touchscreen

Cut protection

Warm lining

Waterproof

Windproof

SIZE		ARTICLE NUMBER	EAN
6	XS	577-6	7340118373423
7	S	577-7	7340118373515
8	M	577-8	7340118373607
9	L	577-9	7340118373690
10	XL	577-10	7340118373782
11	XXL	577-11	7340118373874
12	3XL	577-12	7340118373966

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.