



EAN:	4013288220646	Size:	123x74x27 mm
Part number:	05004177001	Weight:	156 g
Article number:	Bicycle Set 9	Country of origin:	CZ
		Customs tariff number:	82079030

- 10-piece Zyklus Mini set
- Mini ratchet suitable for direct mounting of 1/4" sockets
- Drop-forged full steel design for torques exceeding 65 Nm
- Fine-pitched ratchet mechanism and small return angle of 6°
- Stainless Steel Bits

A lot of bicycle tools in a small space. The sorting of the 9 stainless steel bits by profile and size allows quick access to the right tool. With one Wera Zyklus Mini 1 bit ratchet in a drop-forged solid steel design. The fine toothing mechanism with 60 teeth allows a small return angle of 6° for precise working. The knurl allows fast screwdriving in cramped situations, when there is no space for ratcheting. Easy left/right switching. Ergonomically shaped ratchet head and lever. With Take it easy tool finder with colour coding by size - to help you find the required tool quickly and easily.



Web link
<https://www.wera.de/en/05004177001>

Wera - Bicycle Set 9
 05004177001 - 4013288220646

Wera Werkzeuge GmbH
 Korzelter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

The Zyklop Mini Ratchets



For all difficult-to-access applications.

Rapid screwdriving



High working speeds can be attained with the Zyklop Mini bit ratchet. The thumb wheel is important, enabling more rapid screwdriving, and the lever of the Zyklop Mini only needs to be used for the final tightening of the screw.

The Zyklop Mini



The fine tooth mechanism, with its 60 teeth, allows a small return angle of only 6° - ideal for precision work.

Simple direction change



Simple switching between left/right operations.

Slim design



Its slim design makes it ideal for all particularly confined working situations.

Stainless Steel Bits




Wera stainless steel bits are manufactured out of stainless steel so unsightly rust can be avoided. The stainless steel bits from Wera are vacuum ice-hardened and have the hardness and strength needed for screw connections. There are no limitations to the industrial applications they are suitable for.

Torsion bits



Torsion bits (T) absorb the damaging peak torque loads in the torsion zone. This prevents premature wear and enhances the service life of the bits.

Bits with Take it easy tool finder



Take it easy tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.

Web link

<https://www.wera.de/en/05004177001>

Wera - Bicycle Set 9

05004177001 - 4013288220646

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Set contents:

8001 A Bit Ratchet 1/4", 1/4" x 87 mm



1x 1/4" x 87 mm

3851/1 TS bits, stainless, PH 2 x 25 mm



05071011001

1x PH 2 x 25 mm

3867/1 TS TORX® bits, stainless, TX 10 x 25 mm



05071032001

1x TX 10 x 25 mm

05071035001

1x TX 25 x 25 mm

3840/1 TS bits, stainless, 2 x 25 mm



05071071001

1x 2 x 25 mm

05071072001

1x 2.5 x 25 mm

05071073001

1x 3 x 25 mm

05071074001

1x 4 x 25 mm

05071075001

1x 5 x 25 mm

05071076001¹⁾

1x 6 x 25 mm

1) Without Torsion zone

Web link

<https://www.wera.de/en/05004177001>

Wera - Bicycle Set 9

05004177001 - 4013288220646

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de