


USER'S MANUAL FOR INDUSTRIAL FLOOR FAN

Model Number: FQT-60A



Please read carefully and save these instructions

User instructions

(Please read these instructions carefully and familiarize yourself with your new fan before first use.)

Power

120V~60Hz 320W

Ensure that voltage indicated on the identification plate corresponds with the mains voltage.

Fitting of 3 pin plug

Important: the wires in this mains lead are colored in accordance with the following code:

Green and Yellow	- Earth
Blue	- Neutral
Brown	- Live

As the colors of the wires in the mains lead of this appliance may not correspond with colored markings indentifying the terminals in your plug, proceed as follows:

The wire which is colored **green & yellow** must be connected to the terminal in the plug which is marked with the letter "E" or the earth symbol Or colored **green** or **green& yellow**.

The wire which is colored **blue** must be connected to the terminal which is marked with the letter 'N' or colored **black**.

The wire which is colored **brown** must be connected to the terminal which is marked with the letter 'L' or colored **red**.

PLEASE READ CAREFULLY- ALWAYS MAINTAIN SAFETY WHEN WORKING WITH ANY APPLIANCE

- Check that the mains voltage corresponds with the rating of the appliance before operating.
- To protect against electric shock, do not immerse cords, plugs or appliances in water or any other liquid.
- Do not leave any appliance unattended while it is operating.
- Close supervision is necessary when any appliance is used by or near children or infirm persons.
- Unplug from outlet when not in use or before cleaning. Allow to cool before putting on or taking off any parts.
- Do not operate the appliance with a damaged cord or plug, or after the appliance has been damaged in any manner. If the supply cord or appliance is damaged, it must be replaced by the manufacturer or it is service agent or a similarly qualified person in order to avoid a hazard.
- The use of accessory attachments not recommended by the appliance manufacturer may cause injuries.
- Do not let the cord hang over the edge of a table or counter or let it come into contact with any hot surfaces
- To disconnect-remove the plug from the outlet. Do not pull plug out by the cord.
- Do not use this product for anything other than it's intended use.
- No liability can be accepted for any damage caused by noncompliance with these instructions or any other improper use or mishandling.

- Do not use the appliance without the protective grills.
- Do not attempt to force the grill in order to make the fan turn or stop.
- Never put objects into the grills when the appliance is connected to the mains.
- It is not advisable to expose people(esp.. Babies or older peoples) to a continuous cold air stream for a long time

Operation of your new fan

(WARNING: TO REDUCE THE RISK OF FIRE OR ELECTRICAL SHOCK, DO NOT USED THIS FAN WITH ANY SOLD STATE SPEED CONTROL DEVICE)

ASSEMBLY INSTRUCTIONS

- Remove the packaging material from the fan control box;
- Remove the screws from the two extremities of the base tube.
- Insert the tube into the fan body as shown in Figure ①.
- Align the screws hole and tighten the holding screws onto the base.

NOTE: When installing the control box, make sure the electrical wires are located on the outside of the base.

OPERATION

- Plug the power cord into 120V volt AC wall outlet.
- The 3 speeds system is designed to give you maximum flexibility and to meet all your air circulation needs.
- LOW or MED speed setting can be used for most of your requirements.
 - High speed should only be necessary in exceptional circumstances.
 - Select the desired speed by using the rotary control switch.
 - Adjust to your desired air stream by tilting the fan assembly to the require position.

CARE AND STORAGE

- Turn the control to OFF and unplug the fan before cleaning.
- Use only a soft, damp cloth to clean the fan.
- Do not place the fan in water and never allow water to drip into the Motor Housing.
- Do not use gasoline, paint thinner or other chemicals to clean the fan.
- To clean the fan Blade, Remove the Front grill and Wipe the Blade and Grills.
- Reassemble the fan by snapping the Front Grill into place.
- Store the fan in its original box or cover the fan to protect it from dust.
- Store it in a cool, dry place.

CUSTOMER SERVICE

CONTACT OUR PROFESSIONAL CUSTOMER SUPPORT AT
Kettek2023@outlook.com

Ax1 	Bx2 	Cx1 	Dx1 	Ex4 
Fx2 	Hx2 	Ix2 	Hx2 	 x1

