



jalas® GREEN LINE 6498 NATURE

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2011 S3, SRC

Learn more

FIRST SAFETY BOOT WITH EU-ECOLABEL

First safety boot with EU-Ecolabel. Metal-free boot with nail protection in plasma-treated composite (PTC) textile, toe cap in composite and an insole with dual absorption zones. Upper material: microfiber.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- Water repellent
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)
- Meets the EU flower environmental criteria
- ProNose toe reinforcement
- Ventilating insole
- Bellows tongue
- Oil-resistant outsole
- Metal free
- Anti-static properties
- Stabilizator
- Pull loops
- Free from animal-derived materials

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors, All-year use, Environments with risk for outsole penetration, Metal-free requirements for shoes

PRIMARY AREAS OF USE

Airport work

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile
FITTING Narrow/Regular
COLLECTION Green Line
UPPER MATERIAL Microfiber, Textile
PRONOSE MATERIAL PU
TOECAP MATERIAL Composite
LINING MATERIAL Polyamide
INSOLE JALAS 8303 FX3 Supreme
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Double shock absorption zones in PORON® XRD®
OUTSOLE MATERIAL PU outsole
FASTENING Laces
SHOELACES LENGTH 130 cm
COLOUR Black
NET WEIGHT, (SIZE 42) 1.14 kg

COMPLIANCE

CE Cat. II

ASTM F2413-18
M/I/C/SD 35/PR

EAC TP TC 019:2011

EN ISO 20345:2011
S3, SRC

FEATURES

- Composite toecap
- Nail protection in plasma-treated composite (PTC) textile
- Water repellent
- Oil-resistant outsole
- ProNose toe reinforcement
- Ergothan Shock Absorption System
- Stabilizator
- Anti-static properties
- ESD

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
36	3	4	5	6498-36	6408487418495
37	4	5	6	6498-37	6408487418501
38	5	5.5	6.5	6498-38	6408487418518
39	6	6.5	7.5	6498-39	6408487418525
40	6.5	7.5	8.5	6498-40	6408487418532
41	7	8	9	6498-41	6408487418549
42	8	9	10	6498-42	6408487418556
43	9	9.5	11	6498-43	6408487418563
44	10	10.5	11.5	6498-44	6408487418570
45	10.5	11	12.5	6498-45	6408487418587
46	11	12	13	6498-46	6408487418594
47	12	13	14	6498-47	6408487418600

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.