




EAN: 4013288207609
Part number: 05075680001
Article number: Click-Torque C 3 Set 1

Size: 545x132x95 mm
Weight: 3436 g
Country of origin: TW
Customs tariff number: 82041100

- 13-piece wrench set for torque control applications
- Easy setting and saving of the desired torque value with audible and tactile click when the scale value is reached (click 1)
- Safely quantified force: when the set value is reached, the torque wrench triggers audibly and noticeably (click 2)
- Robust surface-protecting, compact, textile box
- ½"-square. Measuring range: 40-200Nm; precise to ± 3% as per DIN EN ISO 6789-1:2017-07

Click torque wrench set in the unmistakable Wera design. Very robust design with high accuracy as per DIN EN ISO 6789-1: 2017-07. Easy setting and saving of the default values. The audible and tactile snapping on reaching the scale values also facilitates the safe setting of the desired torque values. The robust release mechanism guarantees a clearly audible and tactile trigger signal when the set torque is reached. For clockwise torque-control and with reversible 45-tooth ratchet. Torque wrenches and torque-compatible accessories are packed in an extremely space-saving, robust, surface-friendly textile box. Contains: Click Torque C 3, 1/2", 40 - 200 Nm, 4 sockets with 1/2" drive, 7 hex plus hexagon socket and TORX® bit sockets plus extension.



Web link
<https://www.wera.de/en/05075680001>

Wera - Click-Torque C 3 Set 1
05075680001 - 4013288207609

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Click-Torque Wrench series




Click torque wrench in unmistakable Wera design.

Exact



Precision of ±3 % as per DIN EN ISO 6789-1:2017-07.

Easy and safe




Easy setting and saving of the desired torque value; easy to read on main and fine scales.

Setting with Speed



With audible and tactile locking when the scale values are reached.

Release mechanism



On reaching the desired torque value, an audible and tactile mechanism is triggered.

Bit sockets with retaining function for hexagon socket screws



The clamping of the screw is achieved by a flexible locking ball. The holding function is especially helpful in confined, hard-to-reach spaces, where there is no room for a second hand to secure the screw.

Bit sockets with holding function for TORX® screws



The HF tools developed by Wera are ideal because they feature an optimised geometry of the original TORX® profile. The wedging forces resulting from the surface pressure between the drive tip and the screw profile mean that TORX® screws made according to Camcar Innovations, Michigan, USA specifications are securely held on the tool!

In robust textile box



Robust surface-protecting, compact, textile box

Web link

<https://www.wera.de/en/05075680001>

Wera - Click-Torque C 3 Set 1
05075680001 - 4013288207609

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

Click-Torque C 3 torque wrench with reversible ratchet, 40-200 Nm, 1/2" x 40-200 Nm

	05075622001	1x	1/2" x 40-200 Nm
---	-------------	----	------------------

8790 HMC Zyklop socket with 1/2" drive, 10 x 37 mm

	05003601001	1x	10 x 37 mm
	05003604001	1x	13 x 37 mm
	05003608001	1x	17 x 37 mm
	05003610001	1x	19 x 37 mm

8767 C HF TORX® Zyklop bit socket with 1/2" drive with holding function, TX 30 x 60 mm

	05003833001	1x	TX 30 x 60 mm
	05003834001	1x	TX 40 x 60 mm
	05003835001	1x	TX 45 x 60 mm
	05003836001	1x	TX 50 x 60 mm

8740 C HF Zyklop bit socket with 1/2" drive with holding function, 6 x 60 mm

	05003822001	1x	6 x 60 mm
	05003824001	1x	8 x 60 mm
	05003825001	1x	10 x 60 mm

8794 SC Zyklop extension with free-turning sleeve, short, 1/2", 1/2" x 125 mm

	05003637001	1x	1/2" x 125 mm
			

Web link

<https://www.wera.de/en/05075680001>

Wera - Click-Torque C 3 Set 1
05075680001 - 4013288207609

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de