



|                        |                                        |                               |               |
|------------------------|----------------------------------------|-------------------------------|---------------|
| <b>EAN:</b>            | 4013288229885                          | <b>Size:</b>                  | 200x120x80 mm |
| <b>Part number:</b>    | 05006619001                            | <b>Weight:</b>                | 764 g         |
| <b>Article number:</b> | Kraftform Kompakt VDE 17 RA Imperial 1 | <b>Country of origin:</b>     | CZ            |
|                        |                                        | <b>Customs tariff number:</b> | 82054000      |

- Imperial
- One Kraftform Kompakt VDE 837 i RA bladeholding screwdriver with ratchet functionality (40 teeth, 9° return angle) for interchangeable blades, one 817 VDE bladeholding screwdriver for interchangeable blades
- The 837 i RA bitholding screwdriver with a ratchet integrated in the handle ensures fast and safe working
- High working speed: The ratchet can also be used to "spin" when screwdriving
- Ergonomic intuitive switching to clockwise/counterclockwise or position 0
- VDE blades (157 mm length) with practical spinning function, anti-roll protection and Take it easy tool finder: colour coding by profile and laser-engraved size indication
- Individually tested tools as per IEC 60900
- In a robust folding pouch

17-piece Kraftform Kompakt VDE set. One 837 i RA bladeholding screwdriver with ratchet functionality (40 teeth, 9° return angle), one 817 VDE bitholding screwdriver, 15 VDE blades with Take it easy Tool finder: Colour coding by profile and laser-engraved size indication. Individually tested tools as per IEC 60900. Individually tested in a water quench at 10,000 V for safe working at the approved voltage of 1,000 V. In a robust belt pouch.



#### Web link

<https://www.wera.de/en/05006619001>

Wera - Kraftform Kompakt VDE 17 RA Imperial 1  
05006619001 - 4013288229885

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)




Why is the right tool so often missing at the workplace? The reason: too many tools and overly-heavy tool bags can make it bothersome to carry keep them with you. So for us it was a clear challenge: to develop a tool that is suitable for a whole host of applications and can be easily taken along to the workplace. Our solution: Kraftform Kompakt tools. A handle into which blades with a range of different profiles can be inserted. Compactly and protectively housed in a light and robust textile pouch - and they are even VDE-tested, too.

#### The 837 i RA bladeholding screwdriver with ratchet functionality




The integrated ratchet with fine toothing (40 teeth and a return angle of 9°) eases and accelerates screwdriving without having to reposition the tool.

#### Rapid screwdriving




The ratchet mechanism also allows fast "spinning" while screwdriving.

#### The 817 VDE bladeholding screwdriver




The bitholding screwdriver is suitable solely for Wera VDE blades. Kraftform Plus handle for comfortable ergonomic screwdriving, avoiding blisters and calluses. Hard handle zones for high working speeds, while soft handle zones guarantee a high torque transfer.

#### Take it easy Tool Finder



The Kraftform Kompakt VDE blades are equipped with the Take it easy Tool finder. The colour coding by profile and the laser-engraved size indication make it easy to identify the required tool quickly.

#### Handle/interchangeable blade system




The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

#### PlusMinus screwdrivers



For the use in terminal blocks, control cabinets, switches, relays, sockets etc.

#### VDE interchangeable blade with reduced shaft diameter (iS)



Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

#### Web link

<https://www.wera.de/en/05006619001>

Wera - Kraftform Kompakt VDE 17 RA Imperial 1  
05006619001 - 401328829885

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Set contents:

837 i RA Kraftform blade-holding handle with ratchet functionality, 9 x 115 mm



05057490001

1x 9 x 115 mm



817 VDE Kraftform blade-holding handle, 9 x 98 mm



05003990001

1x 9 x 98 mm



Kraftform Kompakt VDE 62 i Take it easy, PH 1 x 157 mm



05006510001

1x PH 1 x 157 mm

05006511001

1x PH 2 x 157 mm



Kraftform Kompakt VDE 65 i PZ/S Take it easy, # 1 x 157 mm



05006528001

1x # 1 x 157 mm

05006529001

1x # 2 x 157 mm



Kraftform Kompakt VDE 67 i TORX® Take it easy, TX 10 x 157 mm



05006534001

1x TX 10 x 157 mm

05006535001

1x TX 15 x 157 mm

05006536001

1x TX 20 x 157 mm

05006537001

1x TX 25 x 157 mm



Kraftform Kompakt VDE 60 i Take it easy, 0.4 x 2.5 x 157 mm



05006500001

1x 0.4 x 2.5 x 157 mm

05006503001

1x 0.8 x 4 x 157 mm

05006504001

1x 1 x 5.5 x 157 mm

05006505001

1x 1.2 x 6.5 x 157 mm



Kraftform Kompakt VDE 60 iS Take it easy, 0.6 x 3.5 x 157 mm



05006506001

1x 0.6 x 3.5 x 157 mm



Kraftform Kompakt VDE 68 i Take it easy, # 1 x 157 mm



05006543001

1x # 1 x 157 mm

05006544001

1x # 2 x 157 mm



Web link

<https://www.wera.de/en/05006619001>

Wera - Kraftform Kompakt VDE 17 RA Imperial 1  
05006619001 - 4013288229885

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)