




## TEGERA® 106

Learn more

## DURABLE LEATHER, COMFORTABLE FIT

**Comfortable quality leather glove for rough jobs. Durable full grain cowhide on palm for protection against abrasions. Cotton jersey back and liner for improved breathability and sweat management. Elasticated back for better fit. Safety cuff provides better protection to wrist.**

### CHARACTERISTICS

- Durable

### FUNCTIONS

- Reinforced index finger
- Reinforced fingers and thumb



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*

## PREVENTS RISK OF

Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt

## PRIMARY ENVIRONMENTS OF USE

Dirty environments, Harsh environments

## PRIMARY AREAS OF USE

Metalwork, Mining, Wood industry work, Building and construction, Construction, Soil preparation

## PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Basic metals manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Transportation and logistics, Building and construction, Mining and quarrying

## TYPE OF WORK

Heavy weight

## SPECIFICATION

**TYPE** All-round work gloves, Heavy duty gloves
**CATEGORY** Cat. II
**PALM MATERIAL** Full grain cowhide
**BACK MATERIAL** Cotton, Full grain cowhide
**LINING** Half-lined
**LINING MATERIAL** Jersey
**LENGTH** 220-290 mm
**DEXTERITY** 1
**COLOUR** Blue
**PAIRS PER: BUNDLE/CARTON** 6/60
**DISPLAY TYPE** Thread
**FASTENING** Elasticated 180°
**CUFF STYLE** Safety cuff
**CUFF MATERIAL** Textile
**INNER MATERIAL SPECIFICATION** Cotton, Polyester
**OUTER MATERIAL SPECIFICATION** Leather, Cotton

## COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018
2122X

EN 407:2020 (No flame protection)
X1XXXX

ANSI 3 ABR

| SIZE | | ARTICLE NUMBER | EAN |
|---|---|---|---|
| 7 | S | 106-7 | 7392626017245 |
| 8 | M | 106-8 | 7392626010680 |
| 9 | L | 106-9 | 7392626017252 |
| 10 | XL | 106-10 | 7392626010604 |
| 11 | XXL | 106-11 | 7392626002302 |
| 14 | 5XL | 106-14 | 7392626075733 |
| 15 | 6XL | 106-15 | 7392626037427 |

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*