



<b>EAN:</b>	4013288222282	<b>Size:</b>	198x32x32 mm
<b>Part number:</b>	05051583001	<b>Weight:</b>	51 g
<b>Article number:</b>	1060 i VDE	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- Insulated screwdriver for safe working up to 1,000 volts
- Individually tested
- Multi-component Kraftform handle for fast and low-fatigue working
- Handle markings simplify finding and sorting of tools
- The Wera Black Point tip offers an exact fit and optimum corrosion protection

Premium Kraftform VDE screwdriver. Multi-component Kraftform handle for fast and gentle work. The Wera Black Point tip and a sophisticated hardening process guarantee a long usability for the tip, increased corrosion protection and exact fitting accuracy. Individually tested at 10,000 V for safe working at the approved voltage of 1,000 V. The hexagon anti-roll protection avoids screwdrivers from rolling away annoyingly at the workplace. Handles marked for easy identification and sorting of tools.



**Web link**  
<https://www.wera.de/en/05051583001>

Wera - 1060 i VDE  
 05051583001 - 4013288222282

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: [info@wera.de](mailto:info@wera.de)

**Individually tested**



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.

**Ergonomic Kraftform handle**



The multi-component Kraftform handle for quick and low-fatigue working.

**Non-roll feature**



The hexagonal non-roll feature prevents any rolling away at the workplace.

**Identification marking**









The screw profile and tip size identification markings on the handle make it easier to find the right screwdriver in the tool case, or at the workplace.

**Wera Black Point tip**



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.

**Further versions in this product family:**

						
	mm	mm	mm	mm	inch	inch
05051580001	0.4	2.5	80	81	3/32"	3 1/8"
05051582001	0.6	3.5	100	81	9/64"	4"
<b>05051583001</b>	<b>0.8</b>	<b>4.0</b>	<b>100</b>	<b>98</b>	<b>5/32"</b>	<b>4"</b>
05051587001	1.0	5.5	125	98	7/32"	5"

**Web link**

<https://www.wera.de/en/05051583001>

Wera - 1060 i VDE

05051583001 - 4013288222282

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de