



Monoprice™

8K Certified Ultra High-Speed Slim HDMI® Cable – 8K60, 4K120, 48Gbps, HDR, Gold-Plated, Black

Stunning 8K60 Resolution and Smooth 4K120 Playback, in a Compact Form Factor

Enjoy next-generation video and audio performance in a slimmer, more flexible design with these Certified Ultra High-Speed HDMI® Cables. Built to meet the latest HDMI® 2.1 standards, they support 8K at 60Hz and 4K at 120Hz, delivering sharp visuals, vibrant color, and smooth motion for movies, gaming, and streaming. With a 48Gbps bandwidth, they also support advanced features such as HDR, Variable Refresh Rate (VRR), and Auto Low Latency Mode (ALLM), ensuring an immersive entertainment experience and competitive gaming advantage.

The slim profile makes these cables easier to install in tight spaces while maintaining the durability needed for everyday use. Gold-plated connectors resist corrosion and provide reliable signal transmission, while robust shielding minimizes interference for stable, high-quality performance. Official HDMI certification guarantees compliance with industry standards, giving you confidence when connecting to 8K TVs, 4K projectors, gaming consoles, and AV receivers.

Lengths: 3, 4, and 6 feet

- Certified Ultra High-Speed HDMI® Compliance ensures full adherence to HDMI 2.1 specifications for future-proof performance
- Supports 8K at 60Hz and 4K at 120Hz for breathtaking clarity, lifelike detail, and ultra-smooth motion
- 48Gbps bandwidth capacity provides flawless transmission of high-resolution video and immersive multi-channel audio
- HDR support including HDR10 and Dolby Vision™ delivers enhanced contrast, brightness, and color depth
- Slim, flexible design makes routing and installation easier in space-constrained setups
- Gold-plated connectors resist corrosion and maintain long-lasting signal integrity
- Robust shielding reduces electromagnetic interference for stable, uninterrupted performance
- Universal compatibility with 8K TVs, 4K projectors, gaming consoles, streaming devices, and AV receivers



SLIM, SPACE-SAVING DESIGN

Delivers the full performance of an Ultra High-Speed HDMI® cable in a thinner, more flexible build that's ideal for tight installations.



UNMATCHED 8K AND 4K VISUALS

Supports 8K at 60Hz and 4K at 120Hz with 48Gbps bandwidth for crisp detail, fluid motion, and lifelike color.



ADVANCED HDMI 2.1 FEATURES

Unlocks Dynamic HDR, VRR, ALLM, and eARC for an enhanced home theater and gaming experience.

Full Specs

P/N	47904, 47905, 47906
Cable Type	Certified Ultra High-Speed Slim HDMI® Cable
HDMI Version	HDMI 2.1
Bandwidth	Up to 48 Gbps
Resolution Support	Up to 8K at 60Hz, 4K at 120Hz
HDR Support	HDR, HDR10, Dolby Vision™
Audio Support	eARC (Enhanced Audio Return Channel), Dolby Atmos®, DTS:X®
Refresh Rate Features	Variable Refresh Rate (VRR), Auto Low Latency Mode (ALLM)
Connector Type	HDMI Type A (Standard), Male-to-Male
Connector Plating	Gold-Plated
Cable Jacket Material	PVC
Shielding	Multi-Layer Shielding to Minimize EMI Interference
Compliance	HDMI LA Certified, RoHS Compliant, Proposition 65
Available Lengths	3 ft, 4 ft, 6 ft
Color	Black