


**WARNING**

PROPER SET-UP & USE



1. Do not use ladder if your judgment or balance is reduced by age, health, alcohol, or drugs.

2. Designed for use by one person at a time. Do not exceed working load.

3. Do not straddle over ladder top. Do not sit on any part of ladder.

4. Face ladder and use both hands when climbing up or down. Remove jewelry, and wear clean slip-resistant work shoes. Use extreme caution getting on and off ladder.

5. Stand only on front steps of ladder.

6. Lean into or hold onto ladder to maintain three points of contact while working.

7. Do not over-reach. Keep ladder close to work and body centered between side rails. Climb down and move ladder as needed. Do not walk or move ladder while standing on it.

8. Use care if pushing or pulling to side.

9. Do not climb on or off ladder from side unless it is secured against tipping or sideward motion.

10. Have another person hold ladder when possible.

11. Do not use ladder in high winds or storms.

12. Do not spend long periods on a ladder without regular breaks.

13. Never drop or apply an impact load to ladder.

14. Do not let any ladder contact electrical wires.

LE-70740 v0

LE-70741 v0

**WARNING**

PROPER SELECTION

1. Refer to **NOTICE** label for Highest Standing Level, Working Load, and contact information.

2. Select ladder size to reach work without climbing above the Highest Standing Level or over-reaching.

3. Weight of user, tools, and materials shall not exceed Working Load.

4. Use a fiberglass or wood ladder if working with or around electricity.

INSPECTION

1. Inspect before use. Do not use ladders with missing, loose, damaged, or non-operating parts.

2. Make sure locks are in good working order.

3. Replace heavily worn feet and illegible labels. Never make temporary repairs of damaged or missing parts. Remove damaged or worn ladders from service, and contact manufacturer for replacement parts.

4. Keep ladder clean and free of slippery substances.

5. Destroy ladder if exposed to fire or chemical corrosion.

TRANSPORT AND STORAGE

1. Secure ladder when transporting to avoid excessive wear or loading at vehicle support points.

2. Store ladder where dry and protected from unsafe materials, impact, or corrosion damage.

LE-70740 v0

**WARNING**

**PORTABLE STEPLADDER
ESCABEAU PORTATIF**

1. Check for hazards (beneath, around, and above ladder).

2. Check ladder before each use for damages and missing parts. Ladders with damaged or missing parts shall not be used.



3. Place ladder on firm surface.



4. Ensure ladder is level. Either place feet on levelled surface or use manufacturer-approved device to make it level.



5. Lock spreaders. Make sure all legs are secure against movement.



6. Keep centre of chest between the lines delineated by the two sides of the ladder. Do not overreach.



7. Do not stand or sit on top.



8. Keep clear from electrical wiring and devices.

LE-70744 v0

NOTICE

EXTRA HEAVY-DUTY RATING

TYPE IA 300 LBS/136KG

MODEL

6 STEPLADDER

PART NUMBER

99526F-WK

STEPLADDER SIZE:

5' 2" [1.58m]

STEPLADDER WIDTH:

1' 9" [0.54m]

HIGHEST STANDING LEVEL (STEPLADDER):

3' 5" [1.05m]

ANSI A14

FOR ADDITIONAL INSTRUCTIONS ON SAFE LADDER USE SEE

<http://www.laddersafetytraining.org>

MADE IN CHINA

LE-71182 v1

FIBEREXTRA

LE-71183 v0

EXTRA HEAVY DUTY

This product is intended to carry a maximum load of

300 lbs

LOAD RATING

Includes User, Tools and Materials

ANSI A14 TYPE IA

LE-70774 v1



**WARNING**

**AVOID INJURY
DO NOT CLIMB THIS SIDE**

LE-70736 v0

**DANGER**

Follow **ALL** instructions on this ladder, including those under the steps. Falling from ladder may result in injury or death.

LE-70737 v0

**WARNING**

**AVOID INJURY
DO NOT CLIMB THIS SIDE**

LE-70778 v0

**WARNING**

PINCH POINT

LE-70779 v0