



EAN: 4013288187826
Part number: 05004310001
Article number: Kraftform 2go 100

Size: 185x115x240 mm
Weight: 1115 g
Country of origin: CZ
Customs tariff number: 82054000

- Insulated blades for secure work at 1,000 volts
- Multi-component Kraftform handle for high working speeds and ergonomic screwdriving
- Lasertip tips for more secure fit in the screw head
- Hexagonal anti-roll feature against rolling away
- Suitable for docking with the Wera 2go system.

11 VDE-insulated, Kraftform screwdrivers; with Take it easy Tool finder; in the Wera 2go 4 quiver; comes with an adjustable partition element for individual sectioning.



Web link
<https://www.wera.de/en/05004310001>

Wera - Kraftform 2go 100
05004310001 - 4013288187826

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

At the workplace and when out and about



Wera 2go 4 Tool Quiver




The large set-down area improves the stability of the Tool Quiver. Its large handle means that the quiver can be easily transported or simply hung up at the workplace.

Robust and dimensionally stable



The robust and dimensionally stable material is very resistant against cuts and stabs. The tools carried are protected against damage and moisture. This enhances the service life of the tool box.

Clever organisation



The variably adjustable hook-and-loop fastener partition in the Tool Quiver ensures neat and tidy arrangement of the tools.

Perfect system supplement




Thanks to its hook-and-loop fastener zone, the Tool Quiver can be docked with the Wera 2go 1 tool carrier and with the Wera 2go 2 tool container.

Lasertip prevents slipping out




A precisely-focused laser creates a sharp-edged surface structure. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

Individually tested



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.

Take it easy Tool Finder



Colour coding according to profile and size stamp. This enables faster and more reliable selection of the correct tool from the tool case.

Web link

<https://www.wera.de/en/05004310001>

Wera - Kraftform 2go 100

05004310001 - 4013288187826

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Set contents:

Wera 2go 4 Tool Quiver, 165 x 105 mm

05004353001

1x 165 x 105 mm



162 i PH VDE Insulated screwdriver for Phillips screws, PH 1 x 80 mm



05006152001

1x PH 1 x 80 mm

05006154001

1x PH 2 x 100 mm



165 i PZ VDE Insulated screwdriver for Pozidriv screws, PZ 1 x 80 mm

05006162001

1x PZ 1 x 80 mm

05006164001

1x PZ 2 x 100 mm



167 i VDE Insulated screwdriver for TORX® screws, TX 10 x 80 mm

05006170001

1x TX 10 x 80 mm

05006172001

1x TX 15 x 80 mm

05006174001

1x TX 20 x 80 mm



160 i VDE Insulated screwdriver for slotted screws, 0.4 x 2.5 x 80 mm



05006100001¹⁾

1x 0.4 x 2.5 x 80 mm

05006116001

1x 0.8 x 4 x 150 mm

05006121001

1x 1 x 5.5 x 200 mm



1) Without Lasertip

160 iS VDE Insulated screwdriver with reduced blade diameter for slotted screws, 0.6 x 3.5 x 100 mm


05006440001

1x 0.6 x 3.5 x 100 mm



Hook and Loop Fastener Strip 120, 120 x 50 mm

1x 120 x 50 mm



Web link

<https://www.wera.de/en/05004310001>

Wera - Kraftform 2go 100

05004310001 - 4013288187826

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de