Project / Job Name:

Location:

Fixture Type:

Notes:

62-8021 - Silhouette; Medium LED Pendant; 20 Watt; 2700K/3000K/3500K CCT; Matte Black Finish



90+ CRI | DIMMABLE | ETL | FC | RoHS | CCT SELECTABLE | 25,000 HOURS | 3 YEAR WARRANTY | 120-277V | IP 20

GENERAL

Company	NUVO
EA Height	10.03
EA Width	21.25
EA Length	21.25
Mounting Height	1.38
Bulb Included	Integrated
Diameter	6.0
Material	Steel
Status	Active
Style	Contemporary
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	<10%
Up Down Installation	Down
CCT Selectable	Yes
Wattage Selectable	No
Collection	Silhouette
Finish Family	Black
Amps	0.500A
Mounting Diameter	7.13
Lens Finish	Smoked
Lens Material	Glass
Lensed	Yes
Power Factor	>0.9
Sloped Ceiling Compatible	Yes
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	55W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	2700K/3000K/3500K
Dimmable	Yes-Dimmable
Hours Rated	25000
Beam Angle (degree)	120
Color Temp	Warm White to Neutral White
CRI	90+
Dimming Type	Phase cut
Operating Frequency	50/60Hz
Operating Temp	-4F to +140F (-20C to +60C)
Lumens	1600L
Volts	120V-277V
Watts	20W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Matte Black
Housing Color	Matte Black
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Cylinder

ADDITIONAL INFO

Warranty	3-Years
Rated For Enclosed Fixture	No

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923416538
Case Cube	2.621
Case Height	10.03
Case Length	21.25
Case Quantity	1
Case UPC	10045923416535
Case Weight	33.0
Case Width	21.25
EA Cube	2.621
EA Height	10.03
EA Length	21.25
EA Quantity	1
EA Weight	33.0
EA Width	21.25
Pack Type	Kraft Box
Web Height	16.5
Web Width	6.0

COMPLIANCE

Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IC Rated	No
IP Rating	IP20
Location Rating	Dry
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026