



## Technical Data

|                      |                           |
|----------------------|---------------------------|
| Color                | Black                     |
| Sizes Available      | OS                        |
| Packaging            | Bagged Each               |
| Packed               | 72 Pair/Case              |
| Case Dimensions (in) | 18.86 x 10.39 x 11.81     |
| Case Weight (lbs)    | 10.80                     |
| Country of Origin    | Taiwan                    |
| Lens                 | Indoor Outdoor            |
| Frame Style          | Full                      |
| Lens Color           | Clear                     |
| Frame Fit            | Round Face                |
| Lens Coating         | Anti-Scratch, Anti-Fog    |
| Bridge               | Molded                    |
| Temple               | Bayonet                   |
| Base Curve           | 8                         |
| Certifications       | ANSI Z87.1, TAA Compliant |
| Product Circularity  | Recycled via Terracycle   |

## Bouton® Optical Squadron™

Full Frame Safety Glasses with Black Frame, Indoor/Outdoor Lens and Anti-Scratch / Anti-Fog Coating

- Modern and sporty full frame styling
- Ultra flexible temples provide a comfortable fit on larger head sizes
- Frame contains no metal parts
- A variety of lens options for virtually any lighting environment
- ⚠️ **WARNING:** Reproductive Harm - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

## Applications

- Artificial Light
- Indoor/Outdoor Work
- Fork Lift Operation

## SKU Information

| SKU         | FRAME COLOR | LENS        | LENS COLOR | LENS    | UPC          | UPC (INNER)    | UPC (CASE)     |
|-------------|-------------|-------------|------------|---------|--------------|----------------|----------------|
|             |             |             |            | COATING |              |                |                |
| 250-53-0006 | Black       | Mirror Plus | Blue       | AS/AR   | 616314206108 | 01616314206107 | 02616314206106 |
| 250-53-0020 | Black       | Clear       | Clear      | AS/AF   | 616314206078 | 01616314206077 | 02616314206076 |
| 250-53-0021 | Black       | Tinted      | Gray       | AS/AF   | 616314206085 | 01616314206084 | 02616314206083 |
| 250-53-0022 | Black       | I/O         | Clear      | AS/AF   | 616314206092 | 01616314206091 | 02616314206090 |
| 250-53-1024 | Camouflage  | Tinted      | Brown      | AS/AF   | 616314206115 | 01616314206114 | 02616314206113 |

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated