



**MCR
SAFETY**

Law (LW2) Safety Glasses

Value Series Specification Sheet

PRODUCT DESCRIPTION:

This lightweight and fashionable wrap-around lens design offers an excellent orbital seal and a higher level of protection from side impacts due to its greater coverage area. TPR temple inserts that enhance grip and comfort are included on all styles. This series is a dielectric option, meaning that there are no metal pieces in the eyewear. Hi-Vis orange TPR temple inserts are included on our clear, gray, and silver mirror styles. Choose the best safety glasses, choose MCR Safety!



FEATURES:

- Dielectric, no metal parts
- Single lens design with integral side shields for greater orbital seal
- Hybrid Temple Design
- Thermal Plastic Rubber (TPR) temple inserts and nose pads enhance grip and comfort
- Rugged polycarbonate lens filters 99.9% of harmful U.V. rays
- Lightweight frame is comfortable and easy to wear

TECHNICAL DATA FOR: LW210AF

Series	Law (LW2)	ANSI Z87+	Yes
Category	Safety Glasses	CAN/CSA Z94.3	Yes
Dielectric	Yes	AS/NZS 1337.1	Yes
Anti-Fog	Yes	CE EN166	Yes
Scratch Resistant	Yes		
Packaging	White Inner Box		
Case Pack	144	Case Weight	12.564 lb.
Case Dimensions	22.441 x 14.961 x 13.386	Made In	Taiwan

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
LW210	Clear	Duramass Hard Coat	Yes	90	N/A	Clear	Orange

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved



MCR
SAFETY

Law (LW2)

Safety Glasses

Value Series

Specification Sheet

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
LW210AF	Clear	Duramass Anti-Fog	Yes	90	N/A	Clear	Orange
LW212	Gray	Duramass Hard Coat	Yes	13	N/A	Smoke	Orange
LW2120	Green Filter 2.0	Duramass Hard Coat	Yes	30	N/A	Green	Black
LW212AF	Gray	Duramass Anti-Fog	Yes	13	N/A	Smoke	Orange
LW213	Light Blue	Duramass Hard Coat	Yes	68	N/A	Light Blue	Black
LW2130	Green Filter 3.0	Duramass Hard Coat	Yes	12	N/A	Green	Black
LW2130G	Gray Filter 3.0	Duramass Hard Coat	Yes	12	N/A	Gray	Orange
LW214	Amber	Duramass Hard Coat	Yes	80	N/A	Amber	Black
LW2150	Green Filter 5.0	Duramass Hard Coat	Yes	2	N/A	Green	Black
LW2150G	Gray Filter 5.0	Duramass Hard Coat	Yes	2	N/A	Gray	Orange
LW217	Silver Mirror	Duramass Hard Coat	Yes	13	N/A	Smoke	Orange
LW218	Blue Mirror	Duramass Hard Coat	Yes	13	N/A	Smoke	Black
LW219	I/O Clear Mirror	Duramass Hard Coat	Yes	36	N/A	Clear	Black

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved