



PIP® Stromboli™

Cap Style Smooth Dome Hard Hat with Heat Resistant ABS/Polycarbonate Shell, 4-Point Textile Suspension and Swing Wheel-Ratchet Adjustment

- Lightweight shell made with UV stabilized ABS/Polycarbonate shell reduces worker fatigue
- Smooth dome styling is popular in construction, welding and metal working
- Meets -ANSI/ISEA Z89.1 Type I and CSA Z94.1 Type I requirements
- Fulfills Class E Electrical Insulation requirements
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- SURE LOCK wheel adjustment system for one hand size adjustments

Applications

- Mining
- Tunneling
- Demolition
- Utility Work
- Metalworking

Technical Data

Color	Lime, Yellow, Orange, Forest Green, Dark Green, Gray, Steel Blue, Red, Dark Gray, Black, White
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	20.30 x 14.00 x 28.10
Case Weight (lbs)	11.46
Country of Origin	Canada
Shell Material	ABS / Polycarbonate
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Swing Ratchet
Suspension	4 Point Nylon Webbing Cradle
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant
Product Circularity	Recycled via Terracycle

Performance Data

ANSI Type	Type I
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-05

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP841SR-11	Black	OS	620606003290	10616314299770	10620606003297
280-HP841SR-14	Dark Gray	OS	616314981470	10616314791908	20616314981474
280-HP841SR-04	Dark Green	OS	848309040033	10848309040030	20848309040037
280-HP841SR-74	Forest Green	OS	620606003320	10616314299855	10620606003327
280-HP841SR-09	Gray	OS	620606003283	10616314299817	10620606003280
280-HP841SR-45	Lime	OS	620606004242	10616314299893	10620606004249
280-HP841SR-03	Orange	OS	620606003276	10616314299930	10620606003273
280-HP841SR-15	Red	OS	620606003306	10616314300452	10620606003303
280-HP841SR-71	Steel Blue	OS	620606003313	10616314300490	10620606003310
280-HP841SR-01	White	OS	620606003252	10616314300537	10620606003259
280-HP841SR-02	Yellow	OS	620606003269	10616314300537	10620606003266