



TEGERA® 873

Learn more

PALM-DIPPED WITH BLACK NITRILE FOAM

Soft and breathable 15 gg knitted synthetic glove, palm-dipped with nitrile foam for good tactility and better grip. Suitable for light weight work in dry environments. Dirt-masking darkgrey and black colours for extended product use. With food approval (not for fatty food) and Oeko-Tex certificate.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Durable
- Good grip
- Comfortable

FUNCTIONS

- Approved for handling foodstuffs

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Grazes, Scratches, lacerations, Contact with dirt

PRIMARY ENVIRONMENTS OF USE

Dry environments, Moist environments, Dirty environments

PRIMARY AREAS OF USE

Fine assembly, Assembly, Inspection work, Machine operating, Painting, Installation work, Construction, Machine driving, Warehouse work

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Electrical equipment manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Transport equipment manufacturing, Transportation and logistics, Warehousing

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Assembly gloves, Precision work gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 15
LINING MATERIAL Nylon, Spandex
LENGTH 220-260 mm
DEXTERITY 5
GRIP DESIGN Foam grip pattern
COLOUR Black
PAIRS PER: BUNDLE/CARTON 12/120
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL Nitrile foam
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
INNER MATERIAL SPECIFICATION Nylon, Elastane
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN 420:2003
+A1:2009

EAC

EN 388:2016
4132X

SIZE		ARTICLE NUMBER	EAN
9	L	873-9	7392626054783
10	XL	873-10	7392626054790
11	XXL	873-11	7392626054806

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.