



TEGERA® DYNAMIC STRENGTH 7780

Learn more

AGAINST HEAT, COLD AND CUTS

Top quality leather glove for heavy applications and high level of protection. The glove withstands contact heat up to 100°C/212°F, has cut resistance level C and is fully lined. The sewing thread is heat resistant, the seams and the thumb are reinforced. By purchasing this product, you are supporting Leather Working Group certified tanneries.

CHARACTERISTICS

- Highest level of protection
- Very durable

FUNCTIONS

- Withstands contact heat up to 100°C

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Prevents risk of: , Burn injuries, Heat injuries, Cut injuries

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Warm environments, Harsh environments

PRIMARY AREAS OF USE

Foundry, Metalwork

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Oil and gas extraction, Basic metals manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Mining and quarrying

TYPE OF WORK

Heavy weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves
CATEGORY Cat. II
COLLECTION Dynamic Strength
PALM MATERIAL Full grain cowhide
BACK MATERIAL Full grain cowhide of top quality
LINING Fully lined
LENGTH 315-340 mm
DEXTERITY 5
COLOUR White
PAIRS PER: BUNDLE/CARTON 6/60
DISPLAY TYPE Thread
FASTENING Elasticated 180°
CUT RESISTANCE (EN ISO 13997) Cut resistance level C
CUT RESISTANCE (EN ISO 13997) TDM: 12.2 N
INNER MATERIAL SPECIFICATION Para-aramid
OUTER MATERIAL SPECIFICATION Leather, Elastane, Meta-aramid

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 2X33C

EN 407:2020 4131XX

ANSI A3 CUT

ANSI 4 ABR

FEATURES

Cut protection

SIZE		ARTICLE NUMBER	EAN
7	S	7780-7	7340118375533
8	M	7780-8	7340118375625
9	L	7780-9	7340118375717
10	XL	7780-10	7340118375809
11	XXL	7780-11	7340118375892
12	3XL	7780-12	7340118375984
13	4XL	7780-13	7340118376073

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.