



**MCR  
SAFETY**

# 9760 Predator

## Supported / Dipped gloves Specification Sheet

### PRODUCT DESCRIPTION:

The protection the Predator® gloves offer is unmatched in the market giving you the advantage over what you will face at work today. The 9760 Predator® features a premium nitrile palm coating on a soft jersey liner and has a safety cuff for added protection. Treated with ActiFresh®. (Vending Packaged option available - VP9760). Looking for the best work gloves? Look no further than MCR Safety!

### FEATURES:

- Premium nitrile coating on fingers and over knuckles
- Soft jersey lining
- Safety cuff for added protection
- Treated with ActiFresh®
- Component materials comply with all relevant federal regulations for food contact

### APPLICATIONS:

Agriculture, Carpentry, Construction, Demolition, Farming, Forestry, Landscaping, Lumber industry, Material Handling



### TECHNICAL DATA FOR: 9760

<b>Series</b>	Predator
<b>Material Group</b>	Supported
<b>Product Type</b>	Supported / Dipped gloves
<b>Glove Size</b>	Large
<b>Material</b>	Nitrile
<b>Grade</b>	Premium
<b>Lining</b>	Jersey
<b>Thumb Style</b>	Straight
<b>Made In</b>	China,Pakistan

<b>Overall Length</b>	11 in.
<b>EN 388: CE Score - Abrasion</b>	4
<b>EN 388 : CE Score - Cut</b>	2
<b>EN 388 : CE Score - Tear</b>	3
<b>EN 388 : CE Score - Puncture</b>	2
<b>ANSI Cut</b>	A2
<b>ANSI Contact Heat</b>	3 - Less than 392°F

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)


©2021 MCR Safety - All Rights Reserved



**MCR**  
SAFETY

# 9760 Predator

Supported / Dipped gloves  
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9760	Large	10.630	5.020	2.500	39.036 lb.	3.253
9760S	Small	0	0	N/A	33.840 lb.	2.820
9760XL	X - Large	11.023	5.450	2.500	41.076 lb.	3.423
9760M	Medium	10.236	4.760	2.500	35.856 lb.	2.988

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2021 MCR Safety - All Rights Reserved