



EAN:	4013288209580	Size:	235x110x80 mm
Part number:	05134000001	Weight:	571 g
Article number:	Kraftform Micro Big Pack 1	Country of origin:	CZ
		Customs tariff number:	82054000

- 25-piece Kraftform Micro screwdriver set in a robust and compact roll bag
- Kraftform Micro handle for fast and ergonomic working
- Tools with anti-roll protection and rotating cap for fast turning
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Take it easy tool finder: colour coding according to profile and size
- Suitable for electricians, opticians, precision mechanics, jewellers or computer hardware engineers

Wera Micro screwdriver set for fine mechanical screw connections. By supporting the hand on the rotating cap, and by the fast rotating zone below the rotating cap, lightning fast turning is possible. Time-consuming hand switching is eliminated. Storage and transport in a robust roll-bag, so the correct tool is always at hand. With Take it easy tool finder: colour coding by profile and size stamping.



Web link
<https://www.wera.de/en/05134000001>


Wera - Kraftform Micro Big Pack 1
 05134000001 - 4013288209580

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Take it easy Tool Finder



Kraftform Micro handle with rotating cap for rapid spinning



Screwdrivers with Take it easy tool finder: colour coding according to profile and size stamp.

Kraftform Micro handle




Multi-component screwdriver handle for ergonomic working.

The refined screwdriver for electronics technicians




The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The free-turning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.

The precision zone




The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The fast-turning zone



The fast-turning zone just below the rotating cap allows rapid spinning.

Wera Black Point tip



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.

Web link




<https://www.wera.de/en/05134000001>

Wera - Kraftform Micro Big Pack 1
05134000001 - 4013288209580

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de



Set contents:

2050 PH Screwdriver for Phillips screws for electronic applications, PH 000 x 40 mm






	05345290001 ^{1),2)}	1x	PH 000 x 40 mm
	05118019001 ^{1),2)}	1x	PH 00 x 40 mm
	05118026001 ³⁾	1x	PH 0 x 40 mm

1) Optimised for Asian PH screws
 2) On the output side, the blade is turned to a nominal length of 10 mm
 3) Size 0 modified according to JCIS 0 (Japanese Camera Industrial Standard)


2067 TORX® Screwdriver for TORX® screws for electronic applications, TX 5 x 40 mm

	05118040001	1x	TX 5 x 40 mm
	05118042001	1x	TX 6 x 40 mm

2067 TORX® HF Screwdriver with holding function for electronic applications, TX 5 x 40 mm





	05118181001	1x	TX 5 x 40 mm
	05118182001	1x	TX 6 x 40 mm
	05118183001	1x	TX 7 x 60 mm
	05118184001	1x	TX 8 x 60 mm
	05118186001	1x	TX 10 x 60 mm

2067 IPR TORX PLUS® Screwdriver for electronic applications, 1 IPR x 40 mm







	05030160001 ¹⁾	1x	1 IPR x 40 mm
---	---------------------------	----	---------------

1) Without bore hole



2054 Screwdriver for hexagon socket screws for electronic applications, 0.9 x 40 mm

	05118062001	1x	0.9 x 40 mm
	05118064001	1x	1.3 x 40 mm
	05118066001	1x	1.5 x 60 mm
	05118068001	1x	2 x 60 mm


2035 Screwdriver for slotted screws for electronic applications, 0.23 x 1.5 x 40 mm

	05118002001	1x	0.23 x 1.5 x 40 mm
	05118004001	1x	0.30 x 1.8 x 60 mm
	05117997001	1x	0.35 x 2.5 x 40 mm
	05118006001	1x	0.40 x 2 x 60 mm
	05118008001	1x	0.40 x 2.5 x 80 mm
	05118010001	1x	0.50 x 3 x 80 mm


2069 Nutdriver for electronic applications, 4 x 60 mm

	05118120001	1x	4 x 60 mm
	05118126001	1x	5.5 x 60 mm

2072 Kraftform Micro screwdriver for Microstix® screws, m x 40 mm

	05118145001	1x	m x 40 mm
---	-------------	----	-----------

1429 Lifting fork, 1 x 3.5 x 50 mm

	05027456001	1x	1 x 3.5 x 50 mm
---	-------------	----	-----------------

Web link

<https://www.wera.de/en/05134000001>

Wera - Kraftform Micro Big Pack 1
 05134000001 - 4013288209580

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Hook and Loop Fastener Strip 120, 120 x 50 mm

1x 120 x 50 mm



Web link

<https://www.wera.de/en/05134000001>

Wera - Kraftform Micro Big Pack 1
05134000001 - 4013288209580

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de