

BEST PAINTER'S MASKING TAPE

PREMIUM



AmTape® Best Painter's™ Masking Tape by Cellux® delivers sharp, professional paint lines on walls, ceilings, and trim. Made with Cellux® Super Washi and water-based adhesive, it sticks securely to various surfaces and removes cleanly without damage. Perfect for precise masking with water-based paints, stains, and varnishes.



Surfaces

Walls and Ceilings - Drywall – Trim and Moldings – Textured wall surfaces

1 Quick Snapshot (Visual Summary)

Feature	Value
Use	Indoor / Outdoor
Adhesive Type	Acrylic
UV Resistance	Up to 60 days
Clean Removal	Up to 60 days
Paper Type	Advanced Cellux® technology super washi paper
Available color	Blue

3 Ideal Uses

- Ideal for the professional paint industry due to its resistance to all types of paints and solvents.
- Architecture, marquetry and labeling.
- Masking and protection on residential or commercial spaces. Temporary holds for lightweight materials (e.g., paper, cardboard).

2 Technical Performance

Property	Imperial	Metric
Adhesion to steel	11 oz/in	3 N/25mm
Tensile strength	29 lbs/in	50 N/10mm
Residue after removal	Visual inspection	None
Temperature Range	302°F	150°C

4 Premium Insights (Why It Stands Out)

- Cellux® super Washi Paper Technology ensures flexible adhesion for a precise, wrinkle-free application.
- Smart adhesive technology ensures quick stick and consistent hold—even on lightly textured walls.
- Flexible backing adapts to corners, edges, and uneven surfaces for smooth, bubble-free application.
- Specially developed for professional wall painting, delivering ultra-clean paint lines with minimal prep.

5 Product Reference

Customization: OEM branding and special colors available (MOQ required)

SKU	Size / Description	Cases/pallet	Roll/Case
BPT007-18060PK1	0.70"(18mm) x 60yd(54.8m) Blue 60 days outdoor Best Painter's masking tape - individually packaged	64	32
BPT007-24060PK1	0.94"(24mm) x 60yd(54.8m) Blue 60 days outdoor Best Painter's masking tape - individually packaged	64	24
BPT007-36060PK1	1.41"(36mm) x 60yd(54.8m) Blue 60 days outdoor Best Painter's masking tape - individually packaged	64	16
BPT007-48060PK1	1.88"(48mm) x 60yd(54.8m) Blue 60 days outdoor Best Painter's masking tape – individually packaged	64	12

6 Usage Recommendations

- Apply on clean, dry surfaces.
- Press down firmly to ensure full adhesion.
- Remove at a 45° angle after job completion.
- Avoid removing tape when paint is still wet to prevent tearing or lifting.



WE STICK STRONG