



Technical Data



Color	Clear
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	25.39 x 10.83 x 12.80
Case Weight (lbs)	12.35
Country of Origin	Taiwan
Lens	Clear
Frame Style	Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch
Bridge	Molded
Temple	Spatula
Base Curve	10
Certifications	ANSI Z87.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Bouton® Optical Zenon Z-Lyte™ Rimless Safety Glasses with Clear Temple, Clear Lens and Anti-Scratch Coating

- Weighing in at 16 grams, Z-Lyte brings in a new era of lightweight safety eyewear
- Modern wraparound lens style will look great on a variety of users
- Thin temple provides a secure fit without pressure
- ⚠️ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-13

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-09-0000	Clear	Clear	Clear	AS	616314205491	01616314205490	02616314205499
250-09-0001	Gray	Tinted	Gray	AS	616314205507	01616314205506	02616314205505
250-09-0002	Clear	I/O	Clear	AS	616314205514	01616314205513	02616314205512
250-09-0020	Clear	Clear	Clear	AS/AF	616314205521	01616314205520	02616314205529
250-09-0021	Gray	Tinted	Gray	AS/AF	616314205538	01616314205537	02616314205536

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated