



<b>EAN:</b>	4013288181503	<b>Size:</b>	280x44x30 mm
<b>Part number:</b>	05100004001	<b>Weight:</b>	78 g
<b>Article number:</b>	160 i SB	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- Insulated blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Take it easy tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away
- Conical blade

Wera VDE screwdrivers with multi-component Kraftform Plus handle for fast and low-fatigue working: hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Individually tested in water bath at 10,000 volts for secure work at the permissible voltage of 1,000 volts. The tips of the Wera Lasertip screwdrivers are microscopically roughened by laser beams. This rough surface literally bites into the head of the screw. Any unintentional slipping out is therefore a thing of the past. Take it easy tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool. The hexagonal anti-roll feature prevents any bothersome rolling away at the workplace.

**Web link**  
<https://www.wera.de/en/05100004001>

Wera - 160 i SB  
 05100004001 - 4013288181503

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: info@wera.de

**Individually tested**




The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.




The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.

**Impact strength test**



Impact strength tested at -40°C, guaranteeing safety even under extreme conditions.

**Lasertip prevents slipping out**



A precisely-focused laser creates a sharp-edged surface structure. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

**Reduced contact pressure**



Wera Lasertip reduces the contact pressure required and enhances force transfer - meaning less screwdriving effort is required. Screwdriving becomes safer and easier.

**Prevents hand injuries**




The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

**Rapid hand repositioning**



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels through the hand.

**Take it easy Tool Finder**



Screwdrivers with Take it easy tool finder: colour coding according to profile and size stamp.

160 i SB VDE Insulated screwdriver for slotted screws, 1 x 5.5 x 125 mm



Set contents:

160 i VDE Insulated screwdriver for slotted screws, 1 x 5.5 x 125 mm



05006120001

1x 1 x 5.5 x 125 mm



Web link

<https://www.wera.de/en/05100004001>

Wera - 160 i SB

05100004001 - 4013288181503

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)