



EAN:	4013288235176	Size:	385x115x45 mm
Part number:	05343820001	Weight:	1405 g
Article number:	6004 Joker 2 Set 1	Country of origin:	CZ
		Customs tariff number:	82041200

- 2 self-setting spanners with ratchet functionality
- For hexagon screw heads and bolts with sizes 19-32 (metric) and 3/4"-1 1/4" (imperial) and all intermediate sizes with only 2 spanners
- Automatically and continuously gripping hexagonal screws and bolts
- Lever mechanism upon gripping prevents slipping and damage
- With mechanical ratchet functionality for fast and consistent screwdriving without removing the spanner
- Return angle of only 30° through placement in the corner-width rectangular prisms in the open end
- Textile folding pouch made of robust material, protects surfaces from damage, can be docked onto the Wera 2go system


2-piece set. Self-setting Joker 6004 wrenches with ratchet functionality. With its continuous and parallel jaws, the tool replaces several single wrench sizes. For metric (19.0 to 32.0 mm) and imperial (3/4" to 1 1/4") hexagon screws and bolts. The required size is automatically and continuously set when attaching the tool to the hexagon bolt or screw. The integrated lever mechanism securely clamps the hexagon screw or bolt between the jaws, which significantly reduces the risk of slippage or damage. The ratchet feature ensures fast and consistent screwdriving without removing the tool. By using the corner-width rectangular prisms, a return angle of only 30° can be achieved. The single-arm design, in conjunction with the ratchet feature and the corner-width prism, makes it possible to work even in confined spaces. In a robust roll pouch.

Web link
<https://www.wera.de/en/05343820001>

Wera - 6004 Joker 2 Set 1
 05343820001 - 4013288235176


Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Joker 6004: automatically and continuously self-setting



With its automatically and continuously gripping parallel jaws the Joker spanner 6004 covers all dimensions in the respective field of application. The tool automatically finds the required size when placed on the bolt or screw, no setting required.

Joker 6004: gentle to the screw




The parallel smooth jaws of the Joker 6004 allow surface pressure and can thus prevent rounding of the bolt or screw head, which can occur during power transmission via the corners.

Joker 6004: Ratchet mechanism for quick working



The ratchet feature in the jaw ensures fast and consistent screwdriving without removing the tool.

Joker 6004: low return angle



The corner-width rectangular prisms in the jaw allow a return angle of only 30°.

With a practical pouch with hook-and-loop fastener system




Storage and transport in a robust and compact textile folding pouch, so the tool is always close at hand.

Pouches made of mesh material



The mesh pouches hold the tools securely and reliably. The size marking can be seen through the mesh material.

Flexible due to hook-and-loop fastener strips



The textile box features a fleece zone at the back. Using the provided self-adhesive hook-and-loop fastener strips, the textile box can be attached to the Wera 2go components. Or to the wall, shelf or workshop trolley.

Set contents:

6004 Joker XL Self-setting spanner, 19; 20; 21; 22; 24 x 3/4; 25/32; 13/16; 7/8; 15/16" x 256 mm

05020104001

1x 19; 20; 21; 22; 24 x 3/4; 25/32; 13/16; 7/8; 15/16" x 256 mm



6004 Joker XXL Self-setting spanner, 24; 27; 30; 32 x 15/16; 31/32; 1; 1 1/16; 1 1/8; 1 3/16; 1 1/4" x 322 mm

05020102001

1x 24; 27; 30; 32 x 15/16; 31/32; 1; 1 1/16; 1 1/8; 1 3/16; 1 1/4" x 322 mm



Web link

<https://www.wera.de/en/05343820001>

Wera - 6004 Joker 2 Set 1
05343820001 - 4013288235176

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de