



PIP® Traverse™

Industrial Climbing Helmet, Type I, ABS Shell, EPS Foam Impact Liner, Wheel Ratchet Adjustment, with 4-Point Chin Strap

- Ultra-lightweight shell made with ABS material provides superior protection
- EPS foam impact liner helps absorb the forces of top-of-head, front, side, and rear impacts
- Includes an adjustable 4-point cross-over chin strap with quick release buckle for a safe and secure fit
- Rugged SURE-LOCK adjustable wheel ratchet ensures proper suspension performance and fit for all head sizes
- Inner suspension includes comfortable padding for above the brow line
- Meets ANSI Z89.1-2014 Type I, Class E

Technical Data

Color	Navy, Dark Green, Orange, Black, Hi-Vis Yellow, Gray, Red, Yellow, White
Sizes Available	OS
Packaging	Case
Packed	18/Case
Case Dimensions (in)	28.35 x 11.61 x 30.71
Case Weight (lbs)	29.17
Country of Origin	China
Shell Material	ABS
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Micro
Size Adjustment	Wheel Ratchet
Suspension	Foam Cradle System
Chin Strap	4-Point Polyester
Sweatband	Polyester EVA
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, EN 12492

Performance Data

ANSI Type	Type I
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP1490R-11	Black	OS	616314857140	10616314857147	20616314857144
280-HP1490R-04	Dark Green	OS	616314851667	10616314851664	20616314851661
280-HP1490R-09	Gray	OS	616314851582	10616314851589	20616314851586
280-HP1490R-44	Hi-Vis Yellow	OS	616314857508	10616314857505	20616314857502
280-HP1490R-08	Navy	OS	616314906961	10616314906968	20616314906965
280-HP1490R-03	Orange	OS	616314857386	10616314857383	20616314857380
280-HP1490R-15	Red	OS	616314857461	10616314857468	20616314857465
280-HP1490R-01	White	OS	616314856426	10616314856423	20616314856420
280-HP1490R-02	Yellow	OS	616314857263	10616314857260	20616314857267