



EAN:	4013288108821	Size:	157x13x13 mm
Part number:	05118103001	Weight:	18 g
Article number:	2052 Micro	Country of origin:	CZ
		Customs tariff number:	82054000

- Kraftform Micro screwdriver with ballpoint for hexagon socket screws
- Multi-component Kraftform Micro handle with anti-roll feature and rotating cap
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Ballpoint for dependable working even in difficult installation situations
- Take it easy tool finder: colour coding according to profile and size
- E.g. for electricians, opticians, precision mechanics, jewellers or IT hardware fitters

High quality Wera Micro screwdriver for precision mechanical work. Ballpoint profile: the ballpoint drive profile means that it is possible to swivel the tool axis away from the screwdriving axis, thus enabling "round the corner" screwdriving. Rapid twisting is possible by fixing the hand on the twist cap and using the fast-turning zone just below it. This makes time-consuming grip adjustments unnecessary. Power zone with integrated soft zones ensure the transfer of higher tightening and loosening torque. Precision zone for the right angle for adjustment work. The Wera Black Point tip offers high corrosion protection and an exact fit. Take it easy tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.



Web link

<https://www.wera.de/en/05118103001>

Wera - 2052 Micro

05118103001 - 4013288108821

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal


Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Ball tip



Screwdriving jobs in electrical and precision engineering applications are often tedious and time-consuming. We learned from users what is important for them: working speeds, torque, precision - and we then focused particularly on these issues.




The spherical drive profile means that it is possible to swivel the axis of the tool to that of the screw, and therefore enable angled, "around-the-corner" screwdriving jobs.

Kraftform Micro handle




Multi-component screwdriver handle for ergonomic working.

The precision zone




The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone



The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The fast-turning zone




The fast-turning zone just below the rotating cap allows rapid spinning.

The refined screwdriver for electronics technicians



The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The free-turning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.

Take it easy Tool Finder



Screwdrivers with Take it easy tool finder: colour coding according to profile and size stamp.

Further versions in this product family:

						
	mm	inch	mm	mm	mm	inch
05118089001	1.3	-	60	97	3.0	2 3/8"
05118090001	1.5	-	60	97	3.0	2 3/8"
05118092001	2.0	-	60	97	3.0	2 3/8"
05118094001	2.5	-	60	97	4.0	2 3/8"
05118096001	3.0	-	60	97	4.0	2 3/8"
05118098001	-	1/16"	60	97	3.0	2 3/8"
05118100001	-	5/64"	60	97	3.0	2 3/8"
05118102001	-	3/32"	60	97	3.0	2 3/8"
05118106001	-	7/64"	60	97	4.0	2 3/8"
05118103001	-	1/8"	60	97	4.0	2 3/8"

Web link

<https://www.wera.de/en/05118103001>

Wera - 2052 Micro

05118103001 - 4013288108821

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de