



PIP® Dom™

Cap Style Smooth Dome Hard Hat with HDPE Shell, 4-Point Textile Suspension and Swing Wheel-Ratchet Adjustment

- Lightweight shell made with UV stabilized High Density Polyethylene (HDPE) reduces worker fatigue
- Smooth dome shell has a rain trough for extra convenience in adverse weather conditions
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- SURE LOCK wheel adjustment system for one hand size adjustments
- Swing strap suspension enables the wearer to reverse don the hat without having to reinstall the suspension
- Non-chaffing, replaceable foam sweatband for maximum sweat absorption

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications

Technical Data

Color	Black, Orange, Royal, Red, Forest Green, Yellow, Dark Green, Hi-Vis Yellow, Navy, Steel Blue, White, Sky Blue, Gray
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	20.30 x 14.00 x 28.10
Case Weight (lbs)	13.23
Country of Origin	Canada
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Swing Ratchet
Suspension	4 Point Nylon Webbing Cradle
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP341SR-11	Black	OS	620606006680	10616314323710	10620606006687
280-HP341SR-04	Dark Green	OS	620606006611	10616314323758	10620606006618
280-HP341SR-74	Forest Green	OS	620606006765	10616314323758	10620606006762
280-HP341SR-09	Gray	OS	620606006666	10616314323758	10620606006663
280-HP341SR-44	Hi-Vis Yellow	OS	620606006741	10616314412674	10620606006748
280-HP341SR-08	Navy	OS	620606006659	10616314317481	10620606006656
280-HP341SR-03	Orange	OS	620606006604	10616314317481	10620606006601
280-HP341SR-15	Red	OS	620606006710	10616314317528	10620606006717
280-HP341SR-17	Royal	OS	620606006727	10616314317603	10620606006724
280-HP341SR-07	Sky Blue	OS	620606006642	10616314317603	10620606006649
280-HP341SR-71	Steel Blue	OS	620606006758	10616314323871	10620606006755
280-HP341SR-01	White	OS	620606006581	10616314323918	10620606006588
280-HP341SR-02	Yellow	OS	620606006598	10616314323956	10620606006595