


16 AWG

GC018



DIRECT 12 VOLT POWER. 12 VOLT PLUG WITH EYELET TERMINALS.

12V

BATTERY TO 12 VOLT OUT.

Power 12V accessories directly from battery terminals. Permanently attach eyelets to a battery for quick connections and easy access to 12V power.

15A

HIGH CONDUCTIVITY.

Made from a high-conductivity 16AWG 100-percent copper wire and a rated capacity of 15-amperes.

MADE TOUGH

INTEGRATED FUSE. STRAIN RELIEF.

A water-resistant cap protects the female adapter plug socket from the elements. Integrated in-line fuse for added safety. Built-in over-molded strain reliefs. All-copper heavy gauge wire.



NOCO

30339 Diamond Parkway, #102
Glenwillow, OH 44139 | USA
1.800.456.6626

no.co

POWER 12V DEVICES.


TIRE PUMPS, VACUUMS, AND MORE.

Power 12V accessories directly from battery terminals. Permanently attach eyelets to a battery for quick connections and easy access to 12V power.



WATER RESISTANT CAP.

Engineered to withstand all the elements from dirt, water, gasoline, and more. A water resistant cap protects the 12-Volt female socket from the elements.



LIE-FLAT DESIGN.

The GC018's lie-flat eyelet design creates a better battery connection for higher conductivity. The low-set eyelet also reduces the risk of bending or damaging the eyelet or terminal post. New copper-plated eyelets improve conductivity, maximizing performance from the battery charger.

20A MICRO BLADE FUSE


Built-in 20A fuse protection for increased safety. The 20A fuse provides equal protection while being 45% smaller than the previous NOCO 10A Fuse.



THE ALL NEW NOCO 20A FUSE
NEXT TO THE PREVIOUS NOCO 10A FUSE.



WHAT'S IN THE BOX



TECHNICAL SPECIFICATIONS

WIRE SIZE:	16 AWG	
INPUT:	M10 (3/8-Inch) Eyelet Terminals	
FUSE:	20 Amp Micro Blade	
CABLE LENGTH:	24 in (61cm)	
WEIGHT:	0.26 lbs (0.12kg)	
VOLUMETRICS:	Retail Packaging: Dimensions: 2.7" x 2.3" x 7.0" Weight: 0.26 lbs UPC: 0-46221-13087-4	Master Carton: Dimensions: 7.6" x 8.6 x 6.9" Weight: 2.5 lbs Quantity: 36 UCC: 20046221130878
	Inner Carton: Dimensions: 7.3" x 2.6" x 3.0" Weight: 0.33 lbs	Units Per Pallet: 960 Units

NOCO

30339 Diamond Parkway, #102
Glenwillow, OH 44139 | USA
1.800.456.6626

no.co