



jalas® ZENIT EVO 7168

ASTM F2413-18 M/I/C/SD 35/PR ASTM F3445-21 SR EN ISO 20345:2022 S3L, SR, FO, SC

Learn more

GOOD LOOKING AND SAFE ON THE MOVE

A new designed lightweight safety shoe with knitted textile upper and BOA® Fit System. Outstanding ergonomics, padded Memory foam and water repellency means day-long safety and comfort. An oil resistant RPU outer sole gives outstanding grip and a ventilated inner sole keeps feet cool. Features JALAS® aluminium toe cap, plasma-treated textile puncture protection and double impact protection zones in PORON® XRD®.

CHARACTERISTICS

- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption
- Extremely light

FUNCTIONS

- Low weight
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Ventilating insole
- BOA® Fit System
- Water repellent
- Ergonomically shaped
- Conforms with IEC 61340-5-1 (ESD)
- Free from animal-derived materials

BOA DIALED IN. PRECISION FIT.

XRD PROTECTION

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic, Slipping

PRIMARY ENVIRONMENTS OF USE

Outdoors, Indoors, Environments with risk for outsole penetration, Dry environments, Clean environments

SPECIFICATION

TYPE Safety footwear, Low shoes
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile
FITTING Regular
COLLECTION Zenit Evo
UPPER MATERIAL Knitted textile, Microfiber
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester
INSOLE JALAS 8303 FX3 Supreme
INNERSOLE MATERIAL Textile, Soft EVA, Rigid EVA, Polyester-based conductive thread, Neo foam, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL RPU outsole
FASTENING BOA® Fit System
COLOUR Black
NET WEIGHT, (SIZE 42) 1.17 kg

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

ASTM F3445-21
SR

EN ISO 20345:2022
S3L, SR, FO, SC

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- Nail protection in plasma-treated composite (PTC) textile
- Water repellent

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3.5	4	7168-35	6408487528835
36	3	4	5	7168-36	6408487528842
37	4	5	6	7168-37	6408487528859
38	5	5.5	6.5	7168-38	6408487528866
39	6	6.5	7.5	7168-39	6408487528873
40	6.5	7.5	8.5	7168-40	6408487528880
41	7	8	9	7168-41	6408487528897
42	8	9	10	7168-42	6408487528903
43	9	9.5	11	7168-43	6408487528910
44	10	10.5	11.5	7168-44	6408487528927
45	10.5	11	12.5	7168-45	6408487528934
46	11	12	13	7168-46	6408487528941
47	12	13	14	7168-47	6408487528958
48	13	13.5	14.5	7168-48	6408487528965

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.