



TEGERA® DYNAMIC STRENGTH 7799

Learn more

PREMIUM CUT PROTECTION GLOVE

Winter-lined premium cut protection E glove with high-visibility colour. It provides warmth and a high level of protection, with touchscreen functionality allowing you to use your smartphone with the gloves on. Made of top-quality full-grain goat skin, polyester, and stainless-steel fiber yarn. Suitable for all-around work. Exceptionally good fit.

CHARACTERISTICS

- High level of protection
- Perfect fit
- Warm

FUNCTIONS

- For touchscreen
- Reinforced fingers and thumb
- Waterproof

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Prevents risk of: , Cut injuries, Contact with moisture, Contact with cold

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Cold environments

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Mining and quarrying

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE All-round work gloves, Assembly gloves, Cold insulation gloves, Cut resistant gloves
CATEGORY Cat. II
COLLECTION Dynamic Strength
PALM MATERIAL Full grain goatskin of top quality
BACK MATERIAL Spandex
LINING Winter-lined
LINING MATERIAL HPPE, Polyester, Stainless steel fibre yarn
LENGTH 235-260 mm
DEXTERITY 5
COLOUR Orange
PAIRS PER: BUNDLE/CARTON 6/36
CUT RESISTANCE (EN ISO 13997) Cut resistance level E
CUT RESISTANCE (EN ISO 13997) TDM: 30.7 N
INNER MATERIAL SPECIFICATION Stainless steel fibre yarn, Polyethylene, Polyester
MIDDLE MATERIAL SPECIFICATION Thermoplastic polyurethane (TPU)
OUTER MATERIAL SPECIFICATION Leather, Polyester, Elastane

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 2X32E

EN 511:2006 121

ANSI A5 CUT

ANSI 4 ABR

FEATURES

Cut protection

For touchscreen

Warm lining

Waterproof

SIZE		ARTICLE NUMBER	EAN
6	XS	7799-6	7340118374871
7	S	7799-7	7340118374963
8	M	7799-8	7340118375052
9	L	7799-9	7340118375144
10	XL	7799-10	7340118375236
11	XXL	7799-11	7340118375328
12	3XL	7799-12	7340118375410

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.